

Analog Devices - Available KGD Models

Category	Generic	Material	Temp Range	Package	Description
A/D Converters	<a href="#">AD7924</a>	AD7924-KGD-DF	-40C to 85C	Film Frame	4-Channel, 1 MSPS, 12-Bit A/D Converter with Sequencer in 16-Lead TSSOP
	<a href="#">AD7466</a>	AD7466-KGD-DF	-40C to 85C	Film Frame	1.6 V Micro-Power 12-Bit ADC
	<a href="#">AD7766-2</a>	AD7766-2-KGD-WP	-40C to 105C	Wafflepack	24-Bit, 8.5 mW, 109 dB, 128/64/32 kSPS ADCs
	<a href="#">ADT7517</a>	ADT7517-KGD-DF	-40C to 125C	Film Frame	SPI-/I <sup>2</sup> C-Compatible, Temperature Sensor, 4-Channel ADC and Quad Voltage Output
	<a href="#">AD7716</a>	AD7716-DF	-40C to 85C	Film Frame	CMOS, 4-Channel, 22-Bit Data Acquisition System
	<a href="#">AD2S1210</a>	AD2S1210-KGD-CHIPS	-55C to 125C	Wafflepack	10-Bit to 16-Bit R/D Converter with Reference Oscillator
	<a href="#">AD5592R</a>	AD5592R-1-KGD-PT	-40C to 105C	Pocket Tape	12-bit octal I2C DAC/ADC w on-chip ref
	<a href="#">AD7689</a>	AD7689-KGD-PT	-40C to 85C	Pocket Tape	8 ch 250ksps 16bit ADC IC
	<a href="#">AD4003</a>	AD4003-KGD-WP	-40C to 125C	Wafflepack	18-Bit, 2 MSPS, Easy Drive, Differential SAR ADC
Amplifiers	<a href="#">AD8229</a>	AD8229-KGD-CHIPS	-40C to 210C	Wafflepack	1nV/VHz Low Noise 210°C Instrumentation Amplifier
	<a href="#">AD8028</a>	AD8028-KGD-CHIPS	-40C to 125C	Wafflepack	Low Distortion, High Speed Rail-to-Rail Input/Output Amplifier
	<a href="#">AD8065</a>	AD8065-KGD-CHIPS	-40C to 85C	Wafflepack	High Performance, 145 MHz <i>FastFET</i> ™ Op Amp
	<a href="#">AD8202</a>	AD8202W-KGD-R7	-40C to 150C	Pocket Tape	High Common-Mode Voltage, Single-Supply Difference Amplifier
	<a href="#">ADA4897-2</a>	ADA4897-2-KGD-CHIPS	-40C to 125C	Wafflepack	1nV/VHz Low Power Operational Amplifier
	<a href="#">ADA4800</a>	ADA4800-KGD-WP	-40C to 85C	Wafflepack	Low Power, High Speed CCD Buffer Aplifier
	<a href="#">AD8634</a>	AD8634-KGD-CHIPS	-40C to 210C	Wafflepack	High Temperature, Low Noise, RRO Dual Operational Amplifier
	<a href="#">AD8608</a>	AD8608-KGD-CHIP	-40C to 125C	Wafflepack	2.7/5V, CMOS, OP, Low Noise, RRIO, 4X
	<a href="#">ADA4841-2</a>	ADA4841-2KGD-WP	-40C to 125C	Wafflepack	Dual Low Power, Low Noise and Distortion, Rail-to-Rail Output Amplifier
	<a href="#">ADA4841-3</a>	ADA4841-2KGD-PT	-40C to 125C	Pocket Tape	Dual Low Power, Low Noise and Distortion, Rail-to-Rail Output Amplifier
Power Management	<a href="#">ADM7172</a>	ADM7172-4.2-KGD-WP	-40C to 125C	Wafflepack	6.5V, 2A, Ultralow Noise, High PSRR, Fast Transient Response CMOS LDO
Switches & Mutiplexers	<a href="#">ADG798</a>	ADG798-KGD-WP	-55C to 210C	Wafflepack	High Temperature, Low Voltage, 8-Channel Multiplexer
	<a href="#">ADG841</a>	ADG841-KGD-CHIPS	-40C to 125C	Wafflepack	0.28 Ω CMOS 1.65 V to 3.6 V Single SPST Switches in SC70 Closed for a Logic 1 Input
Low Power Comparator	<a href="#">ADCMP371</a>	ADCMP371-KGD-RL7	-40C to 85C	Pocket Tape	General Purpose Comparator W/A Push-Pull Output Stage
Clocks & Timing	<a href="#">AD9832</a>	AD9832-KGD-CHIPS	-40C to 85C	Wafflepack	25 MHz Direct Digital Synthesizer Waveform Generator
D/A Converter	<a href="#">AD5766</a>	AD5766-KGD-PT	-40C to 105C	Pocket Tape	16 channel 16 bit BIPOLAR DAC
RF & Microwave	<a href="#">HMC1168</a>	HMC1168KGD-CHIPS	-40C to 85C	Wafflepack	VCO, GaAs, RF/2, 12.48-13.72GHz