

LINEAR TECHNOLOGY MATERIALS DECLARATION

1tc2054mps5#trmpbf

(Engineering Calculation)

TSOT-23

(printed on: 2020-07-11 21:47:41)

TOTAL MASS (g) :0.012601

COMPONENT MATERIAL	VENDOR/INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.000673	1000000	53407.4648438
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.004485	975000	355917.46875
		Iron (Fe)	7439-89-6	0.000110	24000	8729.30371094
		Phosphorus (P)	7723-14-0	0.000001	300	79.3572998047
		Zinc (Zn)	7440-66-6	0.000003	700	238.071914673
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.004599	1000000	364964.21875
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000635	1000000	50410.5898438
		External Plating Total:		0.000635	1000000	50410.5898438
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000080	1000000	6348.58398438
		Internal Plating Total:		0.000080	1000000	6348.58398438
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000448	750000	35552.0742188
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000149	250000	11824.2382812
		Die Attach Total:		0.000597	1000000	47376.3085938
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.000775	130000	61501.9101562
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.004947	830000	392580.59375
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000209	35000	16585.6757812
		Carbon Black (C)	1333-86-4	0.000030	5000	2380.71899414
		Encapsulation Total:		0.005961	1000000	473048.875
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000056	1000000	4444.00927734
					TOTAL MASS (g) :	0.012601