

LINEAR TECHNOLOGY MATERIALS DECLARATION

lt7000jmse-1#pbf

(Engineering Calculation)

MSOP-Exposed

(printed on: 2020-07-11 22:46:00)

TOTAL MASS (g) : 0.036837

COMPONENT MATERIAL	VENDOR/ INDUSTRY NAMES	CONSTITUENT NAME	CAS NUMBER	CONSTITUENT MASS (g)	CONSTITUENT (PPM) OF MATERIAL	CONSTITUENT (PPM) OF TOTAL PKG.
Active Device	Linear Technology	Silicon (Si)	7440-21-3	0.001989	1000000	53994.59375
Die Coat	Dow Corning	Silicone	69430-27-9	0.000000	0	0
Lead Frame	Cu	Copper (Cu)	7440-50-8	0.013845	975000	375844.71875
		Iron (Fe)	7439-89-6	0.000341	24000	9256.99121094
		Phosphorus (P)	7723-14-0	0.000004	300	108.586402893
		Zinc (Zn)	7440-66-6	0.000010	700	271.466003418
		Nickel (Ni)	7440-02-0	0.000000	0	0
		Silicon (Si)	7440-21-3	0.000000	0	0
		Magnesium (Mg)	7439-95-4	0.000000	0	0
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead Frame Total:		0.014200	1000000	385481.75
Plating	PMI	Exter. Plating Pb	7439-92-1	0.000000	0	0
		Exter. Plating Sn	7440-31-5	0.000710	1000000	19274.765625
		External Plating Total:		0.000710	1000000	19274.765625
		Inter. Plating Ni	7440-02-0	0.000000	0	0
		Inter. Plating Ag	7440-22-4	0.000086	1000000	2334.60766602
		Internal Plating Total:		0.000086	1000000	2334.60766602
Die Attach	ELECTRICALLY CONDUCTIVE ADHESIVE	Silver (Ag)	7440-22-4	0.000684	750000	18568.2773438
		Tin (Sn)	7440-31-5	0.000000	0	0
		Lead (Pb)	7439-92-1	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.000000	0	0
		Indium (In)	7440-74-6	0.000000	0	0
		Metal Oxide		0.000000	0	0
		Antimony (Sb)	7440-36-0	0.000000	0	0
		Resin (EP)		0.000228	250000	6189.42529297
		Die Attach Total:		0.000912	1000000	24757.7011719
Encapsulation	MULTI-AROMATIC RESIN Br/Sb FREE	Resin (EP)		0.002439	130000	66210.5625
		Bromine (Br)	40039-93-8	0.000000	0	0
		Silica (SiO2)	60676-86-0	0.015571	830000	422699.75
		Antimony Trioxide (Sb2O3)	1309-64-4	0.000000	0	0
		Metal Hydroxide		0.000657	35000	17835.3164062
		Carbon Black (C)	1333-86-4	0.000094	5000	2551.78076172
		Encapsulation Total:		0.018761	1000000	509297.375
Bond Wire Estimated	AFW/TANAKA/ Kn	Gold (Au)	7440-57-5	0.000179	1000000	4859.24169922
					TOTAL MASS (g) :	0.036837