

### Product / Package Information

<b>Package</b>	LFCSP - Sawn
<b>Body Size (mm)</b>	3 X 3 X 0.75 (1.5 EP)
<b>Lead Count</b>	12
<b>Terminal Finish</b>	100 Sn
<b>MS Number</b>	MS010587B

### Environmental Information

<b>RoHS Compliant</b>	Yes
<b>High Temperature Compliant</b>	Yes
<b>Halogen Free Compliant</b>	Yes
<b>REACH SVHC Compliant</b>	Yes

### Materials Declaration

#### Molding Compound

Description	Substance	CAS#	Weight (g)	Homogeneous Material Level		Component Level		
				Percentage (%)	PPM	Percentage (%)	PPM	
Other inorganic materials	Silica	60676-86-0	7.22E-03	86.91	869100	35.55		355543
Thermosets	Epoxy & Phenol Resin	Proprietary	1.06E-03	12.78	127800	5.23		52282
Other inorganic materials	Carbon black	1333-86-4	2.57E-05	0.31	3100	0.13		1268
<b>Subtotal</b>			<b>8.30E-03</b>	<b>100.00</b>	<b>1000000</b>	<b>40.91</b>		<b>409094</b>

#### Leadframe

Description	Substance	CAS#	Weight (g)	Homogeneous Material Level		Component Level		
				Percentage (%)	PPM	Percentage (%)	PPM	
Copper & its alloys	Copper	7440-50-8	9.61 E-03	96.40	963989	47.32		473234
Copper & its alloys	Iron	7439-89-6	2.49 E-04	2.50	25006	1.23		12276
Copper & its alloys	Zinc	7440-66-6	5.98 E-05	0.60	6004	0.29		2947
Copper & its alloys	Phosphorus	7723-14-0	4.98 E-05	0.50	5001	0.25		2455
<b>Subtotal</b>			<b>9.97 E-03</b>	<b>100.00</b>	<b>1000000</b>	<b>49.09</b>		<b>490912</b>

#### Internal Leadframe Plating

Description	Substance	CAS#	Weight (g)	Homogeneous Material Level		Component Level		
				Percentage (%)	PPM	Percentage (%)	PPM	
Precious metals	Silver	7440-22-4	2.49 E-05	100.0	1000000	0.12		1227

#### External Leadframe Plating

Description	Substance	CAS#	Weight (g)	Homogeneous Material Level		Component Level		
				Percentage (%)	PPM	Percentage (%)	PPM	
Tin & its alloys	Tin	7440-31-5	4.75 E-04	100.0	1000000	2.34		23377

#### Bond Wires

Description	Substance	CAS#	Weight (g)	Homogeneous Material Level		Component Level		
				Percentage (%)	PPM	Percentage (%)	PPM	
Precious metals	Gold	7440-57-5	4.70E-05	99.0	990000	0.23		2314
Precious metals	Palladium	7440-05-3	4.75E-07	1.0	10000	0.002		23
<b>Subtotal</b>			<b>4.75 E-05</b>	<b>100.0</b>	<b>1000000</b>	<b>0.23</b>		<b>2338</b>

#### Chip

Description	Substance	CAS#	Weight (g)	Homogeneous Material Level		Component Level		
				Percentage (%)	PPM	Percentage (%)	PPM	
Other inorganic materials	Doped Silicon	7440-21-3	1.42 E-03	100.0	1000000	7.01		70130

#### Die Attach

Description	Substance	CAS#	Weight (g)	Homogeneous Material Level		Component Level		
				Percentage (%)	PPM	Percentage (%)	PPM	
Precious metals	Silver	7440-22-4	4.61 E-05	77.71	777100	0.23		2271
Thermoset	Epichlorohydrin-formaldehyde-phenol copolymer	9003-36-5	1.84 E-06	3.11	31100	0.01		91
Other organic materials	Epoxy resin, epichlorohydrin-dimer fatty acid	68475-94-5	1.84 E-06	3.11	31100	0.01		91
Other organic materials	Butyrolactone, gamma-	96-48-0	1.84 E-06	3.11	31100	0.01		91
Other organic materials	Poly(toxypropylene)diamine	9046-10-0	1.84 E-06	3.11	31100	0.01		91
Other organic materials	2,6-Diglycidyl phenyl allyl ether oligomer	Unassigned	1.84 E-06	3.11	31100	0.01		91
Other organic materials	Organosilane	TS ref# 10001	1.84 E-06	3.11	31100	0.01		91
Other inorganic materials	Copper(II) oxide	1317-38-0	1.84 E-06	3.11	31100	0.01		91
Other organic materials	Epoxy resin modifier	TS ref# 10038	3.08 E-07	0.52	5200	0.00		15
<b>Subtotal</b>			<b>5.93 E-05</b>	<b>100.0</b>	<b>1000000</b>	<b>0.29</b>		<b>2922</b>

<b>Package Totals</b>			<b>Weight (g)</b>			<b>Percentage (%)</b>		<b>PPM</b>
			<b>2.03 E-02</b>			<b>100</b>		<b>1000000</b>

Note: The information provided in this declaration are true to the best of ADI's knowledge. ADI derived most of the information listed in this declaration from documents provided by third parties, and assumes no liability to any inaccuracy of such information.



ADI Proprietary