



TOP VIEW



FRONT VIEW



SIDE VIEW

	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	---	0.225	---	5.72
B	0.014	0.023	0.36	0.58
B1	0.038	0.065	0.97	1.65
C	0.008	0.015	0.20	0.38
E	0.220	0.310	5.59	7.87
e	0.100		2.54	
L	0.125	0.200	3.18	5.08
Q	0.015	0.070	0.38	1.78
S	0.005	---	0.13	---
eA	0.300	BSC	7.62	BSC
eB	0.400	BSC	10.16	BSC

	INCHES		MILLIMETERS		N	CASE	PKG CODE
	MIN	MAX	MIN	MAX			
D	---	0.550	---	13.97	8	D4	D8-1
D	---	0.785	---	19.94	14	D1	D14-2
D	---	0.840	---	21.34	16	D2	D16-1, D16-3
D	---	0.960	---	24.38	18	D6	D18-1
D	---	1.060	---	26.92	20	D8	D20-1
D	---	1.280	---	32.51	24	D9	Y24-2, Y24-4

NOTES:

1. DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.
2. MEET MIL STANDARD = 1835D EXCEPT: (A) MAX. D FOR N=8, (B) MAX. Q FOR N=8, 14, 16, AND 24 (C) MAX. A, & (D) MIN. B1
3. N = NUMBER OF PINS
4. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
5. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbFREE (+) PKG. CODES.



TITLE:
PACKAGE OUTLINE,
SIDE BRAZE .300"

APPROVAL
RAMON DE LEON
02/17/10

DOCUMENT CONTROL NO.
21-0047

REV. 1/1
C

-DRAWING NOT TO SCALE-