



TOP VIEW



SIDE VIEW



BOTTOM VIEW

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. N IS THE TOTAL NUMBERS OF TERMINALS.
3. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
4. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
5. DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.15MM AND 0.30MM FROM THE TERMINAL TIP. IF THE TERMINAL HAS THE OPTIONAL RADIUS ON THE OTHER END OF THE TERMINAL, THE DIMENSION b SHOULD NOT BE MEASURED IN THAT RADIUS AREA.
6. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
7. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE EU ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
8. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.

MILLIMETERS			
DIM	MIN	NOM	MAX
A	0.600	0.650	0.700
A1	-0.004	--	0.046
A3	0.120 REF		
D	3.400	3.500	3.600
E	3.400	3.500	3.600
b	0.150	0.200	0.250
b1	1.065	1.115	1.165
b2	1.115	1.165	1.215
b3	0.200	0.250	0.300
b4	0.180 REF		
e	0.500 BSC		
e1	0.325 BSC		
e2	0.650 BSC		
k	0.500 REF		
k1	1.185 REF		
k2	0.150 REF		
k3	0.125 REF		
L	0.300	0.400	0.500
L1	0.550	0.650	0.750
L2	0.700	0.800	0.900
L3	1.400	1.500	1.600
L4	0.150 REF		
N	14		
PKGCODE: F143A3F+2			

-DRAWING NOT TO SCALE-



TITLE:			
FC2QFN PKG, 14L, 3.5x3.5x0.65mm			
APPROVAL	DOCUMENT CONTROL NO.	REV.	1/1
	21-100080	B	