



TOP VIEW

SIDE VIEW

BOTTOM VIEW

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. THE TERMINAL #1 IDENTIFIER AND TERMINAL NUMBERING CONVENTION SHALL CONFORM TO JESD 95-1 SPP-012. DETAILS OF TERMINAL #1 IDENTIFIER ARE OPTIONAL, BUT MUST BE LOCATED WITHIN THE ZONE INDICATED. THE TERMINAL #1 IDENTIFIER MAY BE EITHER A MOLD OR MARKED FEATURE.
5. COPLANARITY APPLIES TO TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATIONS.
6. DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.25 mm AND 0.30 mm FROM TERMINAL TIP. IF THE TERMINAL HAS THE OPTIONAL RADIUS ON THE OTHER END OF THE TERMINAL, THE DIMENSION SHOULD NOT BE MEASURED IN THAT RADIUS AREA.
7. MARKING IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
8. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
9. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODES.
10. PKG CODE: F123A7F+4

	SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS	A	0.827	0.877	0.927
STAND OFF	A1	-0.004	0.02	0.046
MOLD THICKNESS	A2	---	0.75	---
L/F THICKNESS	A3	0.127 REF		
LEAD WIDTH	b	0.15	0.2	0.25
	b1	2.975	3.025	3.08
	b2	1.45	1.5	1.55
	b3	0.35	0.4	0.45
	b4	0.625	0.675	0.73
	b5	0.325	0.375	0.43
	b6	2.1	2.15	2.2
	b7	2	2.05	2.1
BODY SIZE	X	D	3.05 BSC	
	Y	E	7.25 BSC	
LEAD PITCH	e	0.5 BSC		
	e1	0.7 BSC		
	e2	0.65 BSC		
	e3	0.5875 BSC		
	e4	0.505 BSC		
	e5	0.485 BSC		
	e6	1.325 BSC		
	e7	0.7375 BSC		
	e8	0.725 BSC		
LEAD CENTER TO PKG CENTER	e9	0.43 BSC		
LEAD EDGE TO LEAD EDGE	K	0.125 REF		
LEAD LENGTH	L	0.725	0.825	0.925
	L1	0.225	0.325	0.425
	L2	0.925	1.025	1.125
	L3	1.175	1.275	1.375
	L4	0.72	0.82	0.92
PACKAGE EDGE TOLERANCE	aaa	0.1		
MOLD FLATNESS	ccc	0.1		
COPLANARITY	eee	0.08		
LEAD OFFSET	bbb	0.1		
NUMBER OF LEADS	N	12		



TITLE:
PACKAGE OUTLINE, 12L, FC2QFN PKG
3.05x7.25x0.88mm

APPROVAL JIE MAD	DOCUMENT CONTROL NO. 21-100485	REV. B	1/1
---------------------	-----------------------------------	-----------	-----

-DRAWING NOT TO SCALE-