



LASER MARK FOR PIN 1 IDENTIFICATION IN THIS AREA

TOP VIEW




SIDE VIEW



BOTTOM VIEW

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
3. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
4. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND Pb-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
7. Package code is F304B4F+1.



* CONTROLLING DIMENSION : MM

SYMBOL	MILLIMETER		
	MIN.	NOM.	MAX.
A	0.700	0.750	0.800
A1	0.000	—	0.050
A2	—	0.530	0.580
A3	0.203		REF.
b	0.150	0.200	0.250
D	4		BSC
E	4		BSC
L	0.200	0.300	0.400
L1	1.410	1.510	1.610
L2	1.600	1.700	1.800
L3	2.000	2.100	2.200
L4	2.600	2.700	2.800
e	0.400		BSC
e1	0.500		BSC
K1	0.090		BSC
K2	0.200		BSC
K3	0.410		BSC
K4	0.590		BSC
K5	0.600		BSC
K6	0.910		BSC
TOLERANCES OF FORM AND POSITION			
aaa	0.100		
bbb	0.070		
ccc	0.100		
ddd	0.050		
eee	0.080		



TITLE:
PACKAGE OUTLINE, 30L
FC2QFN PKG, 4.0X4.0X0.75mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100487

REV. 1
A

-DRAWING NOT TO SCALE-