



Wireless Integrity Sensing Platform (WISP)-EVAL


To improve avionic asset availability, ADI developed a passive wireless integrity sensing platform (WISP). WISPs are postage stamp-sized crack sensors that use carbon nanotube technology. These sensors can be placed in difficult to access locations on aircraft where cracks are likely to occur (so-called hot spots). The passive sensor status is read wirelessly over an ultra low power Bluetooth® connection by a securely paired handheld reader that also provides wireless power to the sensor.

With no batteries and no wires, WISPs are ready to be installed on new or aging structures.

The first sensor to be integrated with WISP nodes is a carbon nanotube crack gauge, which can provide unprecedented accurate sub-millimeter fatigue crack measurements, even in harsh operating and environmental conditions. Other structural health monitoring (SHM) sensors are also in development. These sensors have well-understood physics, and, when coupled with WISP nodes, they offer a remote inspection alternative for many applications. More generally, WISP architecture will help enable condition-based maintenance for a more efficient approach to sustainment.

Key Features

- ▶ Easy installation: no rewiring or redesign of aircraft needed—can apply immediately to hot spots
- ▶ No power necessary: sensor records via permanent physical changes
- ▶ Carbon nanotube (CNT) polymer nanocomposite for smart, multifunctional sensing material
- ▶ No cables, connectors, or batteries needed for data acquisition
- ▶ Internet of Things (IoT) RFID-like operation



For more information, contact cntmarketingsupport@analog.com.




VISIT ANALOG.COM




AHEAD OF WHAT'S POSSIBLE™

Complete Signal Chain for Structural Health Monitoring



System Components



Specifications

- ▶ Crack sensing element:
 - Thickness: ~200 micron
 - Mass: ~10 mg/cm²
 - Bend radius: ~5 mm
 - Size: 25.4 mm × 25.4 mm
 - Crack length accuracy 0.1 mm to 10 mm: 0.1 mm
 - PoD 90% with 95% confidence level: 1 mm
 - Crack length sensitivity: 0.1 mm
- ▶ BLE transmit power: -20 dBm to +2 dBm
- ▶ BLE data link frequency: 2.4 GHz
- ▶ Platform form factor: 24 mm × 30 mm × 6 mm
- ▶ RF exciter frequency: 5.8 GHz
- ▶ Operating temperature range: -10°C to +65°C
- ▶ Range of operation: 0.5 m to 1 m

Engage with the ADI technology experts in our online support community. Ask your tough design questions, browse FAQs, or join a conversation.



Visit ez.analog.com

Circuits from the Lab reference designs are built and tested by ADI engineers with comprehensive documentation and factory-tested evaluation hardware.

Circuits from the Lab
Reference Designs

Visit analog.com/cftl

For more information, contact cntmarketingsupport@analog.com.



For regional headquarters, sales, and distributors or to contact customer service and technical support, visit analog.com/contact.

©2020 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners.

VISIT ANALOG.COM

Ask our ADI technology experts tough questions, browse FAQs, or join a conversation at the EngineerZone Online Support Community. Visit ez.analog.com.

BR22421-9/20(A)