



TOP VIEW  
GLASS SIDE



BOTTOM VIEW  
LEAD SIDE



SIDE VIEW

COMMON DIMENSIONS			
DIM	MIN	NOM	MAX
A	0.600	0.640	0.680
A1	0.0055	0.0085	0.0115
D	1.965	1.990	2.015
E	1.965	1.990	2.015
e	0.500 BSC		
b	0.180	0.200	0.220
L1	0.380	0.400	0.420
L2	1.325	1.350	1.375
N	6		

NOTES:

- DIMENSIONING AND TOLERANCING CONFORME TO ASME Y14.5M – 2009.
- ALL DIMENSIONS ARE IN MILLIMETERS.
- N IS THE TOTAL NUMBER OF TERMINALS.
- DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30mm FROM TERMINAL TIP. IF THE TERMINAL HAS THE OPTIONAL RADIUS ON THE OTHER END OF THE TERMINAL, THE DIMENSION b SHOULD NOT BE MEASURED IN THAT RADIUS AREA.
- MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
- MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
- PACKAGE CODE: F62A2G+1



TITLE:  
PACKAGE OUTLINE, 6L CHIP ON GLASS  
1.99x1.99x0.64mm BODY

APPROVAL	DOCUMENT CONTROL NO. 21-100042	REV. A	1/1
----------	-----------------------------------	-----------	-----

-DRAWING NOT TO SCALE-