




TOP VIEW



FRONT VIEW



SIDE VIEW



BOTTOM VIEW

COMMON DIMENSIONS			
DIM	MIN	NOM	MAX
A	0.827	0.877	0.927
A1	0	-	0.050
A3	0.127 REF.		
b	0.150	0.200	0.250
b1	0.150	0.200	0.250
D	3.40	3.50	3.60
E	7.65	7.75	7.85
e	0.650 BSC		
e1	0.500 BSC		
e2	0.500 BSC		
L	1.400	1.500	1.300
L1	0.850	0.950	1.050
L2	0.300	0.400	0.500
N	32		
PKG CODE: F327A3+1			

NOTES:

1. DIMENSIONING AND TOLERANCING CONFORME TO ASME Y14.5M - 2009.
2. ALL DIMENSIONS ARE IN MILLIMETERS.
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30mm FROM TERMINAL TIP. IF THE TERMINAL HAS THE OPTIONAL RADIUS ON THE OTHER END OF THE TERMINAL, THE DIMENSION b SHOULD NOT BE MEASURED IN THAT RADIUS AREA.
5. PIN #1 ID ON TOP WILL BE LASER MARKED.
6. BILATERAL COPLANARITY ZONE APPLIES TO THE EXPOSED HEAT SINK SLUG AS WELL AS THE TERMINALS.
7. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
8. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
9. ALL DIMENSIONS APPLY TO PBFREE (+) PKGCODES ONLY.

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 32L
FC2QFN PKG., FLIP CHIP

APPROVAL

DOCUMENT CONTROL NO.
21-100017

REV. A 1/1