



TOP VIEW



SIDE VIEW



BOTTOM VIEW

COMMON DIMENSIONS			
DIM	MIN.	NOM.	MAX.
A	---	---	0.900
A1	0.000	---	0.050
A2	---	0.650	0.700
A3	0.203 REF.		
b	0.130	0.180	0.230
D	6 bsc		
D2	3.320	3.420	3.520
E	6 bsc		
E2	2.900	3.000	3.100
L	0.300	0.400	0.500
e	0.400 bsc		
R	0.065	---	---
TOLERANCES OF FORM AND POSITION			
aaa	0.100		
bbb	0.070		
ccc	0.100		
ddd	0.050		
eee	0.080		
fff	0.100		

NOTES:

1. Unit information : MM
2. Dimension & Tolerance spec(i.e. JEDEC std, 3-sigma or 6 sigma)
3. Notes of special indicator's meaning in the drawing
4. Package Code : F486A6F+1
5. Pb free



TITLE:
PACKAGE OUTLINE, 48L, FCQFN PKG
6.0X6.0X0.90mm

APPROVAL TIAN TIAN	DOCUMENT CONTROL NO. 21-100232	REV. B	1/1
-----------------------	-----------------------------------	-----------	-----

-DRAWING NOT TO SCALE-