



	SYMBOL	COMMON DIMENSIONS		
		MIN.	NDR.	MAX.
TOTAL THICKNESS	A	0.853	0.91	1
SUBSTRATE THICKNESS	A1	0.21		REF
MOLD THICKNESS	A2	0.7		REF
BODY SIZE	D	8		BSC
	E	8		BSC
LEAD WIDTH	W	0.15	0.2	0.25
LEAD LENGTH	L	0.33	0.38	0.43
LEAD WIDTH	W1	1.6	1.65	1.7
LEAD LENGTH	L1	1.6	1.65	1.7
LEAD PITCH	e	0.4		BSC
LEAD PITCH	e1	3.7		BSC
LEAD COUNT	n	68		
LEAD COUNT	n1	4		
EDGE LEAD CENTER TO CENTER	D1	6.4		BSC
	E1	6.4		BSC
BODY CENTER TO CONTACT LEAD	SD	1.85		BSC
	SE	1.85		BSC
PRE-SOLDER		---	---	---
PACKAGE EDGE TOLERANCE	aaa	0.1		
MOLD FLATNESS	bbb	0.2		
COPLANARITY	ddd	0.08		

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. \*N\* IS THE TOTAL NUMBER OF TERMINALS.
3. ALL DIMENSIONS AND TOLERANCES CONFORM TO ANSI Y14.5M-1994.
4. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC #10-0131.
5. ALL DIMENSIONS APPLY TO PbfFREE (+) PKG. CODE ONLY.
6. PACKAGE CODE: L7288M+1.
7. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.



TITLE:  
PACKAGE OUTLINE, 72L LGA  
8X8X0.91 mm

APPROVAL  
WENJIA SONG

DOCUMENT CONTROL NO.  
21-100599

REV. B 1/1

-DRAWING NOT TO SCALE-