


TOP VIEW

SIDE VIEW



BOTTOM VIEW

	SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS	A	0.5	0.55	0.6
STAND OFF	A1	0	0.02	0.05
MOLD THICKNESS	A2	---	0.4	---
L/F THICKNESS	A3	0.152 REF		
LEAD WIDTH	b	0.15	0.2	0.25
	b1	0.2	0.25	0.3
BODY SIZE	X	D		
	Y	E		
LEAD PITCH	e	0.4 BSC		
LEAD LENGTH	L	0.25	0.35	0.45
	L1	0.9	1	1.1
	L2	0.2	0.3	0.4
	L3	0.65	0.75	0.85
	L4	1.15	1.25	1.35
	L5	0.5	0.6	0.7
	L6	0.15 REF		
LEAD TO LEAD	K	0.3 REF		
PACKAGE EDGE TOLERANCE	aaa	0.1		
MOLD FLATNESS	ccc	0.1		
COPLANARITY	eee	0.08		
LEAD OFFSET	bbb	0.07		

NOTES

1. REFER TO JEDEC MO-220
2. COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD
3. BAN TO USE LEVEL 1 ENVIRONMENT-RELATED SUBSTANCES PER JCET SPECIFICATIONS
4. FINISH: Cu/EP • Sn8~20s
5. MAXIM PKG CODE : F243A3F-1
6. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.



TITLE:
PACKAGE OUTLINE, 24L FC2QFN
3x3x0.55mm

APPROVAL

DOCUMENT CONTROL NO.
21-100385

REV. B 1/1

-DRAWING NOT TO SCALE-