



TOP VIEW



SIDE VIEW



BOTTOM VIEW

		SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS		A	0.5	0.55	0.6
STAND OFF		A1	0	0.02	0.05
MOLD THICKNESS		A2	---	0.4	---
L/F THICKNESS		A3	0.152 REF		
LEAD WIDTH		b	0.2	0.25	0.3
		b1	0.7	0.75	0.8
		b2	0.085	0.135	0.185
BODY SIZE	X	D	2 BSC		
	Y	E	2.5 BSC		
LEAD PITCH		e	0.5 BSC		
		e1	0.75 BSC		
LEAD LENGTH		L	0.25	0.3	0.35
		L1	0.3	0.35	0.4
		L2	0.55	0.6	0.65
LEAD EDGE TO PKG EDGE		L3	0.15 REF		
PACKAGE EDGE TOLERANCE		aaa	0.1		
MOLD FLATNESS		ccc	0.1		
COPLANARITY		eee	0.08		
LEAD OFFSET		bbb	0.1		

NOTES

1. REFER TO JEDEC MO-220;
2. COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD;
3. BAN TO USE THE LEVEL 1 ENVIRONMENT-RELATED SUBSTANCES OF JCET SPECS.
4. FINISH: Cu/EP • Sn8~20s
5. MAXIM PKG CODE : F112A2F+1
6. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.



TITLE:
PACKAGE OUTLINE, 11L FC2QFN
2.5x2x0.55mm

APPROVAL TONY LIN	DOCUMENT CONTROL NO. 21-100431	REV. B	1/1
----------------------	-----------------------------------	-----------	-----

-DRAWING NOT TO SCALE-