



TOP VIEW



SIDE VIEW

	SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS	A	0.5	0.55	0.6
STAND OFF	A1	0	0.02	0.05
MOLD THICKNESS	A2	---	0.4	---
L/F THICKNESS	A3	0.152 REF		
LEAD WIDTH	b	0.2	0.25	0.3
	b1	0.25	0.3	0.35
BODY SIZE	X	D	2 BSC	
	Y	E	2 BSC	
LEAD PITCH	e	0.525 BSC		
	e1	0.55 BSC		
LEAD LENGTH	L	0.3	0.35	0.4
	L1	0.25	0.35	0.45
PACKAGE EDGE TOLERANCE	aaa	0.1		
MOLD FLATNESS	ccc	0.1		
COPLANARITY	eee	0.05		
LEAD OFFSET	bbb	0.1		
	ddd	0.05		
CORNER RADIUS	R	0.1 REF		



BOTTOM VIEW

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M.-1994.
3. COPLANARITY APPLIES TO LEADS CORNER LEADS AND DIE ATTACH PAD. PACKAGE IS JEDEC MO-220 COMPLIANT.
4. N IS THE TOTAL NUMBER OF TERMINALS
5. MARKING SHOWN IS FOR PKG. ORIENTATION PURPOSE ONLY.
6. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC #10-0131.
7. ALL DIMENSIONS APPLY TO PBFREE (+) PKG. CODES ONLY.
8. TOTAL THICKNESS NOT INCLUDE SAW BURR.
9. FINISH: Cu/EP • Sn8~20s
10. PACKAGE CODE: F102A2F+2

-DRAWING NOT TO SCALE-


**maxim  
integrated**

TITLE:  
PACKAGE OUTLINE, 10L FC2QFN  
2x2X0.55mm

APPROVAL ZHEN LI	DOCUMENT CONTROL NO. 21-100503	REV. A	1/1
---------------------	-----------------------------------	-----------	-----