


TOP VIEW

SIDE VIEW



BOTTOM VIEW
VIEW M-M

PKG REF.	DIMENSIONS		
	MIN.	NOM.	MAX.
A	0.75	0.80	0.85
A1	0.02	0.05	0.08
A2	0.675 REF		
A3	0.13 REF		
b	0.22	0.27	0.32
D	7.0 BSC		
E	7.0 BSC		
D1	4.4	4.5	4.6
E1	4.4	4.5	4.6
e	0.65 BSC		
e1	0.5 BSC		
e2	2.65 BSC		
e3	3.15 BSC		
N	76		
aaa	0.1		
bbb	0.2		
ccc	0.08		
ddd	0.08		
eee	0.1		

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
3. n IS THE TOTAL NUMBER OF TERMINAL
4. DIMENSION b APPLIES TO METALLIZED TERMINAL.
5. COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD.
6. MARKING IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
7. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC# 10-0131.
8. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
9. PACKAGE CODE: GM7677+1



TITLE:
PKG. OUTLINE, MULTI-ROW QUAD PKG.
76L, 7x7x0.85mm

APPROVAL

DOCUMENT CONTROL NO.
21-100102

REV.
A

1/1

-DRAWING NOT TO SCALE-