



TOP VIEW



SIDE VIEW



BOTTOM VIEW

SYMBOL	COMMON DIMENSIONS		
	MIN.	NDR.	MAX.
A	0.72	0.82	0.92
A1		0.3	REF
A2		0.52	REF
A3		---	REF
D	2.4	2.5	2.6
E	1.9	2	2.1
W	0.25	0.3	0.35
W1	0.25	0.3	0.35
L	0.2	0.25	0.3
L1	0.25	0.3	0.35
e		0.633	BSC
D1		1.9	BSC
E1		1.45	BSC
SD		0.317	BSC
SE		0.725	BSC
aaa		---	
bbb		---	
ddd		0.08	

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M -2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
5. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
6. PACKAGE CODES: F102B2+1, F102B2+2



TITLE:
PACKAGE OUTLINE, 10L, QLGA PKG
2x2.5x0.82mm

APPROVAL
LANBING LIU

DOCUMENT CONTROL NO.
21-100496

REV. 1/1
D