



REF.	DIMENSIONS			NOTE
	MIN.	NOM.	MAX.	
A	0.70	0.75	0.80	
A1	-	-	0.05	
A3	0.20 REF			
b	0.20	0.25	0.30	(5)
D	2.90	3.00	3.10	
E	3.90	4.00	4.10	
E2	2.50	2.60	2.70	
D2	2.20	2.30	2.40	
e	0.50 BSC.			
k	0.30	-	-	
L	0.30	0.40	0.50	
N	10			
ND	5			(6)
PKG CODE	T1034N-1, T1034-2			

NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS, ANGLES IN DEGREES UNLESS OTHERWISE SPECIFIED
- DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
- MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
- (4) A1 CORNER MUST BE IDENTIFIED BY INK/LASER MARK ON TOP PACKAGE, AND CHAMFERED PAD ON BOTTOM PACKAGE.
- (5) DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.25mm AND 0.30mm FROM TERMINAL TIP.
- (6) ND REFERS TO THE NUMBER OF TERMINALS ON THE D SIDE.
- (7) BILATERAL TOLERANCE ZONE IS APPLIED TO EACH SIDE OF THE PACKAGE BODY.
- COPLANARITY APPLIES TO THE EXPOSED HEAT SINK SLUG AS WELL AS THE TERMINALS. COPLANARITY SHALL NOT EXCEED 0.08 mm.
- REFER TO JEDEC MO-229.
- WARPAGE SHALL NOT EXCEED 0.10mm.
- ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbfREE (+) PKG. CODES.



TITLE:  
PACKAGE OUTLINE,  
10L TDFN, 3.0x4.0mm BODY

APPROVAL

DOCUMENT CONTROL NO.  
21-0268

REV.  
D

1/1

-DRAWING NOT TO SCALE-