



TOP VIEW





SIDE VIEW

BOTTOM VIEW

COMMON DIMENSIONS			
DIM	MIN	NOM	MAX
A	0.70	0.75	0.80
A1	0.0	-	0.05
A2	0.20 REF.		
b	0.20	0.25	0.30
D	4.90	5.00	5.10
E	4.90	5.00	5.10
e	0.50 BSC		
k	0.25 REF.		
L	0.30	0.40	0.50
C	0.12 x 45' REF.		
L4	0.31 REF.		
D2	3.60	3.70	3.80
E2	3.60	3.70	3.80
h	0.075	-	0.175
f	0.01	-	0.075
N	32		
ND	8		
NE	8		



FRONT VIEW



NOTES:

1. ALL DIMENSIONS ARE IN mm. ANGLES IN DEGREES.
2. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.
COPLANARITY SHALL NOT EXCEED 0.08 mm.
3. WARPAGE SHALL NOT EXCEED 0.10 mm.
4. PACKAGE LENGTH / PACKAGE WIDTH ARE CONSIDERED AS SPECIAL CHARACTERISTIC. (S)
5. REFER JEDEC MO-220.
6. MAXIM PKG CODE : T3255Y-10C
7. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT,
MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.

-DBRWNISGN00TT00SS0AEE-



maxim
integrated.

TITLE:
PACKAGE OUTLINE, 32L
5X5X0.75 MM, SW TQFN

APPROVAL	DOCUMENT CONTROL NO. 21-100210	REV. A	1/1
----------	-----------------------------------	--------	-----