



TOP VIEW

MILLIMETERS		
SYM	MIN	MAX
A	—	1.20
A1	0.05	0.15
A2	0.90	1.05
b	0.07	0.21
c	0.10	0.20
D	13.30	13.55
D1	11.70	11.90
E	7.90	8.10
e	0.55 BSC	
L	0.30	0.70
L1	0.80 BSC	
PKG CODE	Z28-3, Z28-4	



SEE DETAIL 'A'
SIDE VIEW



DETAIL A

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
3. DETAILS OF PIN 1 IDENTIFIER ARE OPTIONAL BUT ONE HALF OF ITS AREA MUST BE LOCATED WITHIN THE ZONE INDICATED.
4. LEADS SHALL BE COPLANAR WITHIN 0.1mm
5. MEETS JEDEC MO-183
6. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbFREE (+) PKG. CODES.

-DRAWING NOT TO SCALE-

MAXIM

TITLE:
PACKAGE OUTLINE,
28L TSOP(1), 8.0x13.4mm BODY

APPROVAL
RAFAEL AGUIRRE
03/18/10

DOCUMENT CONTROL NO.
21-0273

REV. 1/1
B