



TOP VIEW




SIDE VIEW



BOTTOM VIEW

67- $\phi 0.26 \pm 0.03$   
 $\phi 0.05$  (M) S AB



| PKG. CODE | E    |      | D    |      | DEPOPULATED BUMPS |
|-----------|------|------|------|------|-------------------|
|           | MIN  | MAX  | MIN  | MAX  |                   |
| W674A2+1  | 2.62 | 2.72 | 4.32 | 4.42 | NONE              |

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is  $\pm 0.02\text{mm}$  unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.

-DRAWING NOT TO SCALE-

**MAXIM**

TITLE:  
 PACKAGE OUTLINE, 67L WLP PKG.  
 0.4mm STAGGERED PITCH

|                                  |                                 |           |     |
|----------------------------------|---------------------------------|-----------|-----|
| APPROVAL<br>TIE WANG<br>07-14-08 | DOCUMENT CONTROL NO.<br>21-0215 | REV.<br>C | 1/2 |
|----------------------------------|---------------------------------|-----------|-----|

BUMP BALL COORDINATES

|    | X      | Y     |
|----|--------|-------|
| A2 | 0.849  | 1.980 |
| A4 | 0.283  | 1.980 |
| A6 | -0.283 | 1.980 |
| A8 | -0.849 | 1.980 |
| B1 | 1.131  | 1.697 |
| B3 | 0.566  | 1.697 |
| B5 | 0.000  | 1.697 |
| B7 | -0.566 | 1.697 |
| B9 | -1.131 | 1.697 |
| C2 | 0.849  | 1.414 |
| C4 | 0.283  | 1.414 |
| C6 | -0.283 | 1.414 |
| C8 | -0.849 | 1.414 |
| D1 | 1.131  | 1.131 |
| D3 | 0.566  | 1.131 |
| D5 | 0.000  | 1.131 |
| D7 | -0.566 | 1.131 |
| D9 | -1.131 | 1.131 |
| E2 | 0.849  | 0.849 |
| E4 | 0.283  | 0.849 |
| E6 | -0.283 | 0.849 |
| E8 | -0.849 | 0.849 |
| F1 | 1.131  | 0.566 |
| F3 | 0.566  | 0.566 |
| F5 | 0.000  | 0.566 |
| F7 | -0.566 | 0.566 |
| F9 | -1.131 | 0.566 |

|    | X      | Y      |
|----|--------|--------|
| G2 | 0.849  | 0.283  |
| G4 | 0.283  | 0.283  |
| G6 | -0.283 | 0.283  |
| G8 | -0.849 | 0.283  |
| H1 | 1.131  | 0.000  |
| H3 | 0.566  | 0.000  |
| H5 | 0.000  | 0.000  |
| H7 | -0.566 | 0.000  |
| H9 | -1.131 | 0.000  |
| J2 | 0.849  | -0.283 |
| J4 | 0.283  | -0.283 |
| J6 | -0.283 | -0.283 |
| J8 | -0.849 | -0.283 |
| K1 | 1.131  | -0.566 |
| K3 | 0.566  | -0.566 |
| K5 | 0.000  | -0.566 |
| K7 | -0.566 | -0.566 |
| K9 | -1.131 | -0.566 |
| L2 | 0.849  | -0.849 |
| L4 | 0.283  | -0.849 |
| L6 | -0.283 | -0.849 |
| L8 | -0.849 | -0.849 |
| M1 | 1.131  | -1.131 |
| M3 | 0.566  | -1.131 |
| M5 | 0.000  | -1.131 |
| M7 | -0.566 | -1.131 |
| M9 | -1.131 | -1.131 |

|    | X      | Y      |
|----|--------|--------|
| N2 | 0.849  | -1.414 |
| N4 | 0.283  | -1.414 |
| N6 | -0.283 | -1.414 |
| N8 | -0.849 | -1.414 |
| P1 | 1.131  | -1.697 |
| P3 | 0.566  | -1.697 |
| P5 | 0.000  | -1.697 |
| P7 | -0.566 | -1.697 |
| P9 | -1.131 | -1.697 |
| R2 | 0.849  | -1.980 |
| R4 | 0.283  | -1.980 |
| R6 | -0.283 | -1.980 |
| R8 | -0.849 | -1.980 |

-DRAWING NOT TO SCALE-

|   |                                 |           |     |
|---|---------------------------------|-----------|-----|
|  |                                 |           |     |
| TITLE:<br>PACKAGE OUTLINE, 67L WLP PKG.<br>0.4mm STAGGERED PITCH                      |                                 |           |     |
| APPROVAL<br>TIE WANG<br>07-14-08  | DOCUMENT CONTROL NO.<br>21-0215 | REV.<br>C | 2/2 |