



TOP VIEW



BOTTOM VIEW



J-J' Cross section

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W2256A6+1	6.28	6.48	6.07	6.27	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is $\pm 0.02\text{mm}$ unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.

-DRAWING NOT TO SCALE-

MAXIM

TITLE:
PACKAGE OUTLINE
225 BUMPS WLP PKG. 0.4mm PITCH

APPROVAL TIE WANG 4/14/10	DOCUMENT CONTROL NO. 21-0393	REV. B	1/1
---------------------------------	---------------------------------	-----------	-----