

PCN10_0021 Qualification

TEST NAME	CONDITIONS	SAMPLE SIZE	RESULTS
High Temperature Operating Life Test (HTOL)	960 Hours max operating temp	28 (0)	Pass
Temperature cycling test (TCT) 500 Cycles	T min. storage -5C to T max storage +5C (-45C to +90C)	20 (0)	Pass