



Certificate: 2162710
Project: 70046795

Master Contract: 205078
Date Issued: 2016-10-26

Device (SOIC 16W RW package)	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2			

where x and y may each be a letter differentiating devices with different performance grades. Z, if used, indicates the lead-free version. Suffix ab is a 2 digit number denoting specific supply voltage combinations. Suffix EP at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.

Notes:

1. These devices meet basic insulation requirements for 780Vrms for CSA 60950-1-07+A1+A2 and IEC 60950-1 2nd Ed.+A1+A2.
2. These devices meet reinforced insulation requirements for 390Vrms for CSA 60950-1-07+A1+A2 and IEC 60950-1 2nd Ed.+A1+A2. (pollution degree 2, material group III)
3. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. for 300Vrms, overvoltage category III for basic insulation and 150Vrms, overvoltage category III for reinforced insulation, the devices meet clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6 and 10. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
4. Case material: Multiple mold compounds have been evaluated. All meet at least material group II.
5. Evaluated by thermal cycling and other tests for a temperature rating of 105C.
6. The creepage and clearance has been evaluated for altitudes ≤ 2000m, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

APPLICABLE REQUIREMENTS

- Component Acceptance Notice 5A (CA 5A) - Announcement of Extension of the Component Acceptance Service for Optocouplers and Related Devices
- CAN/CSA-C22.2 No 14-13 - Industrial Control Equipment
- CAN/CSA-C22.2 No 60950-1-07+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements (Bi-national Standard, with UL 60950-1)
- IEC 60950-1 2nd Ed.+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
- EN 60950-1:2006+A1+A12+A2 - Information Technology Equipment - Safety - Part 1: General Requirements

- Clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10
of
CAN/CSA-C22.2 No. 61010-1-12+A1 2015 - Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1: General Requirements



Certificate: 2162710
Project: 70046795

Master Contract: 205078
Date Issued: 2016-10-26

and
IEC 61010-1:2010 3rd Ed.

(Tri-national standard, with UL 61010-1 Ed. 3 and ANSI/ISA-61010-1 (82.02.01)

- Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1: General Requirements



Supplement to Certificate of Compliance

Certificate: 2162710

Master Contract: 205078 (205078)

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description
70046795	2016-10-26	Update for alternative mould compound and leadframe
2569045	2012-10-23	Correction to insulation material cat. no. I-8124ER
2326159	2010-11-08	Transfer of 6xxx models to 2326157
2187706	2009-06-23	Addition of Similar Models ADuM600x, ADuM620x, ADuM640x and Evaluation to 601-1
2162710	2009-05-26	Original Component Acceptance