



产品认证证书

信息技术设备、音视频设备和通信技术设备用光电耦合器 电气性能产品认证

证书编号: CQC26001517323

发证日期: 2026 年 08 月 05 日

有效期至: 2031 年 08 月 04 日

委托人名称	Analog Devices, Inc.
及注册地址	804 Woburn StreetWilmingtonMA 美国
制造商名称	Analog Devices, Inc.
及注册地址	804 Woburn StreetWilmingtonMA 美国
生产企业名称	Analog Devices Gen Trias, Inc
及生产地址	Sandoval St. Gateway Business Park , Javalera , General Trias , Cavite , 菲律宾 4107
产品名称和系列、 规格、型号	I2C 隔离器 ADuM1252ASA+,ADuM1253ASA+,ADuM1254ASA+,ADuM1255ASA+ : 外部爬电距离 : 4mm, 通过 125°C热循环测试, 基本绝缘:最大工作电压: 400V 有效值, 565V 峰值。抗电强 度试验电压: 3000V 有效值, 4242V 峰值(适用于海拔 5000 米及以下)
产品标准和技术要求	GB 4943.1-2022
认证模式	型式试验+初始工厂检查+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

刘江



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



中国质量认证中心有限公司
中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666
http://www.cqc.com.cn



CERTIFICATE OF PRODUCT CERTIFICATION

PRODUCT CERTIFICATION FOR ELECTRICAL PERFORMANCE OF PHOTOELECTRIC COUPLER
USED IN INFORMATION TECHNOLOGY EQUIPMENT, AUDIO/VIDEO EQUIPMENT AND
COMMUNICATION TECHNOLOGY EQUIPMENT

CERTIFICATE NO.: CQC26001517323

Valid from: Aug.05,2026

Valid until:Aug.04,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT Analog Devices, Inc.
804 Woburn StreetWilmingtonMA USA

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Analog Devices, Inc.
804 Woburn StreetWilmingtonMA USA

NAME AND LOCATION OF THE FACTORY Analog Devices Gen Trias, Inc
Sandoval St. Gateway Business Park , Javalera , General Trias , Cavite , Philippines 4107

PRODUCT NAME, MODEL AND SPECIFICATION I2C Isolator
ADuM1252ASA+,ADuM1253ASA+,ADuM1254ASA+,ADuM1255ASA+ : external creepage 4mm,
Passing the 125°C thermal cycle test, basic insulation: maximum operating voltage: 400V RMS,
565V peak. Dielectric strength test voltage: 3000V RMS, 4242V peak (Altitude up to 5000m)

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB 4943.1-2022

TYPE OF CERTIFICATION SCHEMES Type testing of product + initial factory inspection + follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666
<http://www.cqc.com.cn>