



产品认证证书

证书编号: CQC16001150402

发证日期: 2026 年 01 月 14 日
有效期至: 2028 年 04 月 17 日

委托人名称 亚德诺投资有限公司
及注册地址 上海市黄浦区湖滨路 222 号 11 层 (实际楼层为 10 层) 1107 室

制造商名称 Analog Devices
及注册地址 804 Woburn StreetWilmingtonMA 美国

生产企业名称 Analog Devices Gen. Trias
及生产地址 Sandoval St. Gateway Business Park Javalera, General Trias Cavite, 菲律宾 4107

产品名称和系列、规格、型号 数字隔离器
见附件 (仅适用于海拔 5000 米及以下)

产品标准和技术要求 GB 4943.1-2022

认证模式 型式试验+初始工厂检查+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。
本证书为变更证书, 证书首次颁发日期: 2016 年 08 月 23 日
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



中国质量认证中心有限公司
中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666
<http://www.cqc.com.cn>



产品认证证书

证书编号: CQC16001150402

第 1 页 / 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

1) ADUM4400ARWZ、ADUM4400BRWZ、ADUM4400CRWZ、ADUM4401ARWZ、ADUM4401BRWZ、ADUM4401CRWZ、ADW80035ARWZ、ADUM4402ARWZ、ADUM4402BRWZ、ADUM4402CRWZ、ADUM4400WARWZ、ADUM4400WBRWZ、ADUM4401WARWZ、ADUM4401WBRWZ、ADUM4402WARWZ、ADUM4402WBRWZ。

外部爬电距离: 7.7mm, 通过热循环测试, 加强绝缘: 最大工作电压: 380V 有效值、537V 峰值; 基本绝缘: 最大工作电压: 760V 有效值、1075V 峰值。

2) ADUM4400ARIZ、ADUM4400BRIZ、ADUM4400CRIZ、ADUM4401ARIZ、ADUM4401BRIZ、ADUM4401CRIZ、ADUM4402ARIZ、ADUM4402BRIZ、ADUM4402CRIZ。

外部爬电距离: 8.3mm, 通过热循环测试, 加强绝缘: 最大工作电压: 410V 有效值、578V 峰值, 基本绝缘: 最大工作电压: 820V 有效值、1159V 峰值。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC16001150402

Valid from: Jan.14,2026

Valid until: Apr.17,2028

NAME AND REGISTERED ADDRESS OF THE APPLICANT Analog Devices (China) Holdings Co., Ltd.
Room 1107, 11th floor (Actual 10th floor) , #222 Hubin Road, Huangpu District, Shanghai

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Analog Devices
804 Woburn StreetWilmingtonMA, USA

NAME AND LOCATION OF THE FACTORY Analog Devices Gen. Trias
Sandoval St. Gateway Business Park Javalera, General Trias Cavite, Philippines 4107

PRODUCT NAME, MODEL AND SPECIFICATION Digital Isolator
See Appendix (Altitude up to 5000m)

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB 4943.1-2022

TYPE OF CERTIFICATION SCHEMES Type testing of product + initial factory inspection + follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.

Date of original issued: Aug.23,2016

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666
<http://www.cqc.com.cn>



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC16001150402

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

1) ADUM4400ARWZ、ADUM4400BRWZ、ADUM4400CRWZ、ADUM4401ARWZ、ADUM4401BRWZ、ADUM4401CRWZ、ADW80035ARWZ、ADUM4402ARWZ、ADUM4402BRWZ、ADUM4402CRWZ、ADUM4400WARWZ、ADUM4400WBRWZ、ADUM4401WARWZ、ADUM4401WBRWZ、ADUM4402WARWZ、ADUM4402WBRWZ :

External creepage distance: 7.7mm , thermal cycling test; Reinforced insulation: Maximum operating voltage: 380V rms, 537V peak; Basic insulation: Maximum operating voltage: 760V rms, 1075V peak.

2) ADUM4400ARIZ、ADUM4400BRIZ、ADUM4400CRIZ、ADUM4401ARIZ、ADUM4401BRIZ、ADUM4401CRIZ、ADUM4402ARIZ、ADUM4402BRIZ、ADUM4402CRIZ :

External creepage distance: 8.3mm , thermal cycling test; Reinforced insulation: Maximum operating voltage: 410V rms, 578V peak; Basic insulation: Maximum operating voltage: 820V rms, 1159V peak.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE