



Certificate of Compliance

Certificate: 70051637

Master Contract: 205078

Project: 80044794

Date Issued: 2020-05-29

Issued To: Analog Devices Inc.
804 Woburn St
Wilmington, Massachusetts, 01887-3462
United States

Attention: Mark Cantrell

The products listed below are eligible to bear the CSA Mark shown with adjacent indicator▲



Issued by: Martin Buchanan
Martin Buchanan, P. Eng.

PRODUCTS

CLASS - C907330 - ELECTRONIC COMPONENTS Optoisolators and non-optical isolating devices

Component Acceptance of Optoisolator Like Magnetic Coupling Devices:

Device	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
(SOIC 16W RW package) ADuM13xyzBRWZ ADuM14xyzBRWZ ADuM23xyzBRWZ ADuM24xyzBRWZ AD71255BRWZ AD71256BRWZ AD71257BRWZ	3.75 3.75 5.0 5.0 5.0 5.0 5.0	125	CSA 14-18 tb35, 6.2.1.4.1, 6.2.1/6.2.12, 6.8.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7	-	-	7.8



Certificate: 70051637
Project: 80044794

Master Contract: 205078
Date Issued: 2020-05-29

Device	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1 3 rd Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014/A11:2017 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2			
(SOIC 16W RI package) ADuM23xyzBRIZ ADuM24xyzBRIZ	5.0 5.0	125	CSA 14-18 tb35, 6.21.4.1, 6.2.1/6.2.12, 6.8.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1 3 rd Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014/A11:2017 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2	-	-	8.3



Certificate: 70051637

Project: 80044794

Master Contract: 205078

Date Issued: 2020-05-29

where x is 0, 1 or 2 for the number of reverse channels, y is D for input disable or E for output enable, z is for fail safe output state with 0 for low and 1 for high and Z, if used, indicates the lead-free version. Suffix EP at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.

Notes:

1. The RW devices meet basic insulation requirements for 780Vrms and RI devices meet 830Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14 and IEC 60950-1 2nd Ed.+A1+A2 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
2. The RW devices meet reinforced insulation requirements for 390Vrms and RI devices meet 415Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14 and IEC 60950-1 2nd Ed.+A1+A2 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
3. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. for 600Vrms, overvoltage category III for RW devices and overvoltage category IV for RI devices for basic insulation, the devices meet clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
4. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. the RW and RI devices meet 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. (pollution degree 2, material group III)
5. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 2 MOPP for 237.5Vrms for RW devices and 250V for RI devices, the devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
6. Case material: 575Vrms with erosion depth 0.079mm, meets material group II.
7. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
8. The creepage and clearance has been evaluated for altitudes $\leq 2000\text{m}$, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

APPLICABLE REQUIREMENTS

CAN/CSA-C22.2 No 14-18	-	Industrial Control Equipment
CAN/CSA-C22.2 No 60950-1-07+A1+A2	-	Information Technology Equipment - Safety - Part 1: General Requirements (Bi-national Standard, with UL 60950-1)
CAN/CSA-C22.2 No. 62368-1-14	-	Audio/video, information and communication technology equipment— Part 1: Safety requirements
IEC 60950-1 2 nd Ed.+A1+A2	-	Information Technology Equipment - Safety - Part 1: General Requirements
IEC 62368-1:2014 Ed. 2	-	Audio/video, information and communication technology equipment— Part 1: Safety requirements
EN 60950-1:2006+A1+A12+A2	-	Information Technology Equipment - Safety - Part 1: General Requirements
EN 62368-1:2014/A11:2017	-	Audio/video, information and communication technology equipment - Part 1: Safety requirements (IEC 62368-1:2014, modified)



Certificate: 70051637
Project: 80044794

Master Contract: 205078
Date Issued: 2020-05-29

Clauses 6.7.1.3, 6.7.2.1 or K.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 of
CAN/CSA C22.2 No. 61010-1-12, UPD1: 2015, UPD2: 2016, AMD1: 2018 - Safety Requirements for
Electrical Equipment for Measurement, Control, and Laboratory Use, Part
1: General Requirements (Tri-national standard, with UL 61010-1 Ed. 3
(2012), AMD1: 2018 and ANSI/ISA-61010-1 (82.02.01))

IEC 61010-1:2010 Ed. 3.1:2017 01 - Safety Requirements for Electrical Equipment for Measurement, Control
and Laboratory Use - Part 1: General Requirements

Clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7
of
CAN/CSA C22.2 60601-1:14 - Medical Electrical Equipment Part 1: General requirements for basic safety
and general performance (Adopted IEC60601-1:2005 Edition 3.0
+Amendment 1, 2012-07, MOD)
and
IEC60601-1:2005 Ed 3.0+A1 - Medical Electrical Equipment Part 1: General requirements for basic
safety and general performance