



产品认证证书

证书编号: CQC18001192420

发证日期: 2023 年 09 月 01 日
有效期至: 2028 年 08 月 31 日

委托人名称 Analog Devices, Inc
及注册地址 804 Woburn Street, Wilmington, MA 美国

制造商名称 Analog Devices, Inc
及注册地址 804 Woburn Street, Wilmington, MA 美国

生产企业名称 Analog Devices Gen. Trias
及生产地址 Gateway Business Park, Javalera, Geb. Trias, Cavite, 菲律宾

产品名称和系列、规格、型号 数字隔离器
见附件

产品标准和技术要求 GB 4943.1-2022

认证模式 产品型式试验+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。
本证书为变更证书, 证书首次颁发日期: 2018 年 06 月 21 日
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





产品认证证书

证书编号: CQC18001192420

第 1 页 / 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

ADuM250N1BRIZ, ADuM250N1BRIZ-RL, ADuM250N0BRIZ, ADuM250N0BRIZ-RL,
ADuM251N1BRIZ, ADuM251N1BRIZ-RL, ADuM251N0BRIZ, ADuM251N0BRIZ-RL,
ADuM252N1BRIZ, ADuM252N1BRIZ-RL, ADuM252N0BRIZ, ADuM252N0BRIZ-RL,
ADuM260N1BRIZ, ADuM260N1BRIZ-RL, ADuM260N0BRIZ, ADuM260N0BRIZ-RL,
ADuM261N1BRIZ, ADuM261N1BRIZ-RL, ADuM261N0BRIZ, ADuM261N0BRIZ-RL,
ADuM262N1BRIZ, ADuM262N1BRIZ-RL, ADuM262N0BRIZ, ADuM262N0BRIZ-RL,
ADuM263N1BRIZ, ADuM263N1BRIZ-RL, ADuM263N0BRIZ, ADuM263N0BRIZ-RL,
外部爬电距离: 8.3mm, 通过热循环测试, 基本绝缘或附加绝缘: 最大工作电压: 830V 有效值, 1174V
峰值; 加强绝缘: 最大工作电压: 415V 有效值, 587V 峰值 (仅适用于海拔 5000 米及以下)



中国质量认证中心



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC18001192420

Valid from: Sep.01,2023

Valid until:Aug.31,2028

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT** Analog Devices.Inc
804 Woburn StreetWilmingtonMA USA

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER** Analog Devices.Inc
804 Woburn StreetWilmingtonMA USA

**NAME AND LOCATION
OF THE FACTORY** Analog Devices Gen. Trias
Gateway Business Park, Javalera, Geb. Trias, Cavite, Philippines

**PRODUCT NAME, MODEL
AND SPECIFICATION** Digital Isolator
see annex

**THE STANDARDS AND
TECHNICAL REQUIREMENTS
FOR THE PRODUCTS** GB 4943.1-2022

**TYPE OF CERTIFICATION
SCHEMES** Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.

Date of original issued: Jun.21,2018

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC18001192420

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

ADuM250N1BRIZ , ADuM250N1BRIZ-RL , ADuM250N0BRIZ , ADuM250N0BRIZ-RL ,
ADuM251N1BRIZ , ADuM251N1BRIZ-RL , ADuM251N0BRIZ , ADuM251N0BRIZ-RL ,
ADuM252N1BRIZ , ADuM252N1BRIZ-RL , ADuM252N0BRIZ , ADuM252N0BRIZ-RL ,
ADuM260N1BRIZ , ADuM260N1BRIZ-RL , ADuM260N0BRIZ , ADuM260N0BRIZ-RL ,
ADuM261N1BRIZ , ADuM261N1BRIZ-RL , ADuM261N0BRIZ , ADuM261N0BRIZ-RL ,
ADuM262N1BRIZ , ADuM262N1BRIZ-RL , ADuM262N0BRIZ , ADuM262N0BRIZ-RL ,
ADuM263N1BRIZ , ADuM263N1BRIZ-RL , ADuM263N0BRIZ , ADuM263N0BRIZ-RL ,

外部爬电距离 : 8.3mm , 通过热循环测试 , 基本绝缘或附加绝缘 : 最大工作电压 : 830V 有效值 , 1174V 峰值 ; 加强绝缘 : 最大工作电压 : 415V 有效值 , 587V 峰值 (仅适用于海拔 5000 米及以下)



CHINA QUALITY CERTIFICATION CENTRE