



Certificate of Compliance

Certificate: 70120613

Master Contract: 205078 (205078)

Project: 70120613

Date Issued: 2017-11-30

Issued to: Analog Devices Inc.
804 Woburn St
Wilmington, Massachusetts 01887-3462
USA
Attention: Mark Cantrell

The products listed below are eligible to bear the CSA Mark shown with adjacent indicator ▲



Issued by: Martin Buchanan
Martin Buchanan, P. Eng.

PRODUCTS

CLASS - C907330 - ELECTRONIC COMPONENTS-Optoisolators

Component Acceptance of Optoisolator Like Magnetic Coupling Devices:

Device (SOIC 16N package)	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
ADuM150N0BRZ ADuM150N1BRZ ADuM151N0BRZ ADuM151N1BRZ ADuM152N0BRZ ADuM152N1BRZ ADuM160N0BRZ ADuM160N1BRZ ADuM161N0BRZ ADuM161N1BRZ ADuM162N0BRZ ADuM162N1BRZ ADuM163N0BRZ ADuM163N1BRZ	3.0	125	CSA 14-13 Tbl 35, 6.2.1.1, 6.2.1.1/6.2.10, 6.8.1.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2 61010-1-12+A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014 Ed. 2 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 5.4.9.1, 4.1.2	-	-	4.0



Certificate: 70120613
Project: 70120613

Master Contract: 205078
Date Issued: 2017-11-30

Device (SOIC 16N package)	Ratings		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
ADuM150N0WBRZ ADuM150N1WBRZ ADuM151N0WBRZ ADuM151N1WBRZ ADuM152N0WBRZ ADuM152N1WBRZ ADuM160N0WBRZ ADuM160N1WBRZ ADuM161N0WBRZ ADuM161N1WBRZ ADuM162N0WBRZ ADuM162N1WBRZ ADuM163N0WBRZ ADuM163N1WBRZ			61010-1 3 rd Ed A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2			

where Z, if used, indicates the lead-free version. Suffix EP at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.

Notes:

1. These devices meet basic insulation requirements for 400Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14, IEC 60950-1 2nd Ed.+A1+A2 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
2. These devices meet reinforced insulation requirements for 200Vrms for CSA 60950-1-07+A1+A2, CSA 62368-1-14, IEC 60950-1 2nd Ed.+A1+A2 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
3. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. for 300Vrms, overvoltage category III for basic insulation the devices meet clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
4. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. these devices meet 150V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. (pollution degree 2, material group III)
5. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 1 MOPP for 250Vrms, the devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.
6. Case material: 575Vrms with erosion depth 0.079mm, meets material group II.
7. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
8. The creepage and clearance has been evaluated for altitudes ≤ 2000m, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

APPLICABLE REQUIREMENTS

Certificate: 70120613

Master Contract: 205078

Project: 70120613

Date Issued: 2017-11-30

- CAN/CSA-C22.2 No 14-13 - Industrial Control Equipment
- CAN/CSA-C22.2 No 60950-1-07+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements (Bi-national Standard, with UL 60950-1)
- CAN/CSA-C22.2 No. 62368-1-14 - Audio/video, information and communication technology equipment— Part 1: Safety requirements
- IEC 60950-1 2nd Ed.+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
- IEC 62368-1:2014 Ed. 2 - Audio/video, information and communication technology equipment— Part 1: Safety requirements
- EN 60950-1:2006+A1+A12+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
- Clauses K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10
of
CAN/CSA-C22.2 No. 61010-1-12+A1 2015 - Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1: General Requirements (Tri-national standard, with UL 61010-1 Ed. 3 and ANSI/ISA-61010-1 (82.02.01)
- and
IEC 61010-1:2010 3rd Ed. - Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1: General Requirements
- Clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7
of
CAN/CSA C22.2 60601-1:14 - Medical Electrical Equipment Part 1: General requirements for basic safety and general performance (Adopted IEC60601-1:2005 Edition 3.0 +Amendment 1, 2012-07, MOD)
- and
IEC60601-1:2005 Ed 3.0+A1 - Medical Electrical Equipment Part 1: General requirements for basic safety and general performance