



产品认证证书

证书编号: CQC18001192421

发证日期: 2023 年 11 月 24 日
有效期至: 2028 年 11 月 23 日

委托人名称 Analog Devices, Inc.
及注册地址 804 Woburn Street Wilmington MA 美国

制造商名称 Analog Devices, Inc.
及注册地址 804 Woburn Street Wilmington MA 美国

生产企业名称 Analog Devices Gen Trias, Inc
及生产地址 Sandoval St. Gateway Business Park, Javalera, General Trias, Cavite, 菲律宾 4107

产品名称和系列、规格、型号 数字隔离器
见附件

产品标准和技术要求 GB 4943.1-2022

认证模式 产品型式试验+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。
本证书为变更证书, 证书首次颁发日期: 2018 年 06 月 21 日
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





产品认证证书

证书编号: CQC18001192421

第 1 页 / 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

ADuM140D1BRQZ, ADuM140D1BRQZ-RL7, ADuM140D0BRQZ, ADuM140D0BRQZ-RL7,
ADuM140E1BRQZ, ADuM140E1BRQZ-RL7, ADuM140E0BRQZ, ADuM140E0BRQZ-RL7,
ADuM141D1BRQZ, ADuM141D1BRQZ-RL7, ADuM141D0BRQZ, ADuM141D0BRQZ-RL7,
ADuM141E1BRQZ, ADuM141E1BRQZ-RL7, ADuM141E0BRQZ, ADuM141E0BRQZ-RL7,
ADuM141E1WBRQZ, ADuM141E1WBRQZ-RL7,
ADuM142D1BRQZ, ADuM142D1BRQZ-RL7, ADuM142D0BRQZ, ADuM142D0BRQZ-RL7,
ADuM142E1BRQZ, ADuM142E1BRQZ-RL7, ADuM142E0BRQZ, ADuM142E0BRQZ-RL7,
ADuM142E1WBRQZ, ADuM142E1WBRQZ-RL7,

外部爬电距离: 3.2mm, 通过热循环测试, 基本绝缘或附加绝缘: 最大工作电压: 320V 有效值, 453V 峰值 (仅适用于海拔 5000 米及以下)



中国质量认证中心



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC18001192421

Valid from: Nov.24,2023

Valid until:Nov.23,2028

NAME AND REGISTERED ADDRESS OF THE APPLICANT Analog Devices, Inc.
804 Woburn Street Wilmington MA USA

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Analog Devices, Inc.
804 Woburn Street Wilmington MA USA

NAME AND LOCATION OF THE FACTORY Analog Devices Gen Trias, Inc
Sandoval St. Gateway Business Park, Javalera, General Trias, Cavite, Philippines 4107

PRODUCT NAME, MODEL AND SPECIFICATION digital isolators
see annex

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB 4943.1-2022

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.

Date of original issued: Jun.21,2018

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC18001192421

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

ADuM140D1BRQZ , ADuM140D1BRQZ-RL7 , ADuM140D0BRQZ , ADuM140D0BRQZ-RL7 ,
ADuM140E1BRQZ , ADuM140E1BRQZ-RL7 , ADuM140E0BRQZ , ADuM140E0BRQZ-RL7 ,
ADuM141D1BRQZ , ADuM141D1BRQZ-RL7 , ADuM141D0BRQZ , ADuM141D0BRQZ-RL7 ,
ADuM141E1BRQZ , ADuM141E1BRQZ-RL7 , ADuM141E0BRQZ , ADuM141E0BRQZ-RL7 , ADuM141E1WBRQZ ,
ADuM141E1WBRQZ-RL7,
ADuM142D1BRQZ , ADuM142D1BRQZ-RL7 , ADuM142D0BRQZ , ADuM142D0BRQZ-RL7 ,
ADuM142E1BRQZ , ADuM142E1BRQZ-RL7 , ADuM142E0BRQZ , ADuM142E0BRQZ-RL7 , ADuM142E1WBRQZ ,
ADuM142E1WBRQZ-RL7,

外部爬电距离：3.2mm，通过热循环测试，基本绝缘或附加绝缘：最大工作电压：320V 有效值，453V 峰值（仅适用于海拔 5000 米及以下）



CHINA QUALITY CERTIFICATION CENTRE