



# Certificate of Compliance

**Certificate:** 80137946                      **Master Contract:** 205078  
**Project:** 80193080                      **Date Issued:** 2024-03-20  
**Issued to:** Analog Devices Inc.  
804 Woburn St  
Wilmington, Massachusetts 01887-3462  
United States  
**Attention:** Ivy Mae Tejero

*The products listed below are eligible to bear the CSA Mark shown with adjacent indicator "Triangle symbol"*



**Issued by:**  
Martin Buchanan  
Martin Buchanan, P. Eng.

**PRODUCTS**

C907330 ELECTRONIC COMPONENTS - Optoisolators and non-optical isolating devices

Component Acceptance of Optoisolator Like Devices:

Device	Rating		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)



Certificate: 80137946

Master Contract: 205078

Project: 80193080

Date Issued: 2024-03-20

Device	Rating		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
SOIC16W (RW-16) ADuM340E0BRWZ ADuM340E1BRWZ ADuM341E0BRWZ ADuM341E1BRWZ ADuM342E0BRWZ ADuM342E1BRWZ ADuM340E0WBRWZ ADuM340E1WBRWZ ADuM341E0WBRWZ ADuM341E1WBRWZ ADuM342E0WBRWZ ADuM342E1WBRWZ	5.7	125	CSA 14-18 tb35, 6.21.4.1, 6.2.1/6.2.12, 6.8.1 62368-1:19 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 (R2022)+A1+A2 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7  IEC 62368-1:2018 Ed. 3 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1 3 <sup>rd</sup> Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:2005 Ed 3.0+A1+A2 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7  EN 62368-1:2020+A11:2020 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4	-	-	7.8



Certificate: 80137946

Master Contract: 205078

Project: 80193080

Date Issued: 2024-03-20

Device	Rating		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
QSOP16 (RQ-16) ADUM340E0BRQZ ADuM340E1BRQZ ADuM341E0BRQZ ADuM341E1BRQZ ADuM342E0BRQZ ADuM342E1BRQZ ADUM340E0WBRQZ ADuM340E1WBRQZ ADuM341E0WBRQZ ADuM341E1WBRQZ ADuM342E0WBRQZ ADuM342E1WBRQZ	3.0		CSA 14-18 tb35, 6.21.4.1, 6.2.1/6.2.12, 6.8.1 62368-1:19 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 (R2022)+A1+A2 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7  IEC 62368-1:2018 Ed. 3 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1 3 <sup>rd</sup> Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:2005 Ed 3.0+A1+A2 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7  EN 62368-1:2020+A11:2020 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4	-	-	3.2

where Z if used indicates the lead-free version. Suffix EP if present at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.

Notes:

All Devices

1. Case material: material group I.
2. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
3. The creepage and clearance has been evaluated for altitudes ≤ 2000m, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

SOIC16W (RW-16) RW Devices:

1. The devices meet basic insulation requirements for 780Vrms and reinforced insulation requirements for 390Vrms for CSA 62368-1:19. IEC 62368-1:2018 Ed. 3 and EN62368-1:2020. (pollution degree 2, material group III)
2. For CSA 61010-1-12+A1 and IEC 61010-1 3<sup>rd</sup> Ed. the devices meet 600Vrms for basic insulation and 300V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
3. For CSA 60601-1:14 (R2022) and IEC 60601-1:2005 Ed 3.0+A1+A2 for 2 MOPP for 237.5Vrms, the devices meet clauses 8.5.5.1,



**Certificate:** 80137946

**Master Contract:** 205078

**Project:** 80193080

**Date Issued:** 2024-03-20

8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.

QSOP16 (RQ-16) RQ Devices:

1. The devices meet basic insulation requirements for 320Vrms and reinforced insulation requirements for 160Vrms for CSA 62368-1:19. IEC 62368-1:2018 Ed. 3 and EN62368-1:2020. (pollution degree 2, material group III)
2. For CSA 61010-1-12+A1 and IEC 61010-1 3<sup>rd</sup> Ed. the devices meet 300Vrms for basic insulation and 150V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
3. For CSA 60601-1:14 (R2022) and IEC 60601-1:2005 Ed 3.0+A1+A2 for 1 MOPP for 150Vrms, the devices meet clauses 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.

**APPLICABLE REQUIREMENTS**

CSA C22.2 No. 62368-1:19+Upd.1 (Third Edition) - Audio/video, information and communication technology equipment — Part 1: Safety requirements - Third Edition; Update No. 1: October 2021

IEC 62368-1:2018 - Audio/video, information and communication technology equipment – Part 1: Safety requirements - Edition 3.0

EN 62368-1: 2020/A11:2020 - Audio/video, information and communication technology equipment - Part 1: Safety requirements - Incorporates Amendment A11: 2020

CSA C22.2 No. 61010-1-12, UPD1:2015, UPD2:2016, AMD1:2018 - Safety requirements for electrical equipment for measurement, control, and laboratory use — Part 1: General requirements

CSA C22.2 60601-1:14 (R2022) - Medical electrical equipment - Part 1: General requirements for basic safety and essential performance - Third Edition

IEC 60601-1:2005/AMD1:2012/AMD2:2020 - Medical electrical equipment – Part 1: General requirements for basic safety and essential performance - Edition 3.2; Consolidated Reprint; Incorporates Amendment 1: 2012, Corrigenda 1: 12/2012, Corrigenda to Amendment 1: 07/2014, Interpretation 1: 04/2008, Interpretation 2: 01/2009, and Interpretation 3: 05/2013 and Amendment 2: 08/2020

CSA C22.2 No. 14-18 (Thirteenth Edition) - Industrial control equipment - Thirteenth Edition



**Certificate:** 80137946


**Master Contract:** 205078

**Project:** 80193080

**Date Issued:** 2024-03-20

Notes:

Products certified under Class(es) C907330 have been certified under CSA's ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC). [www.scc.ca](http://www.scc.ca)





## *Supplement to Certificate of Compliance*

**Certificate:** 80137946

**Master Contract:** 205078

*The products listed, including the latest revision described below,  
are eligible to be marked in accordance with the referenced Certificate.*

### **Product Certification History**

---

<b>Project</b>	<b>Date</b>	<b>Description</b>
80193080	2024-03-20	Update to 80137946 to add QSOP package devices
80137946	2023-06-05	Original Component Acceptance of Models ADuM34xExBRWZ and ADuM34xExWBRWZ (SOIC 16 W) 5.7kV