



# 产品认证证书

证书编号: CQC25001485291

发证日期: 2025 年 09 月 18 日  
有效期至: 2030 年 09 月 17 日

**委托人名称** Analog Devices, Inc.  
**及注册地址** 804 Woburn StreetWilmingtonMA 美国

**制造商名称** Analog Devices, Inc.  
**及注册地址** 804 Woburn StreetWilmingtonMA 美国

**生产企业名称** Analog Devices Gen Trias, Inc  
**及生产地址** Sandoval St. Gateway Business Park, Javalera, General Trias, Cavite, 菲律宾 4107

**产品名称和系列、规格、型号** RS-485 隔离器  
ADM2561EBRNZ,ADM2563EBRNZ,ADM2565EBRNZ,ADM2567EBRNZ 外部爬电距离:  
8.3mm, 通过 125℃热循环测试, 加强绝缘: 最大工作电压: 415V 有效值, 587V 峰值。基本  
绝缘: 最大工作电压: 830V 有效值, 1174V 峰值。抗电强度试验电压: 3000V 有效值, 4242V  
峰值。ADM2861EBRNZ,ADM2863EBRNZ,ADM2865EBRNZ,ADM2867EBRNZ, 外部爬电距离:  
8.3mm, 通过 125℃热循环测试, 加强绝缘: 最大工作电压: 415V 有效值, 587V 峰值。基本  
绝缘: 最大工作电压: 830V 有效值, 1174V 峰值。抗电强度试验电压: 5700V 有效值, 8061V  
峰值(适用于海拔 5000 米及以下)

**产品标准和技术要求** GB 4943.1-2022

**认证模式** 型式试验+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。  
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 ( www.cnca.gov.cn ) 查验证书信息



签发:



谢肇煦

中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE



中国质量认证中心有限公司  
中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666  
<http://www.cqc.com.cn>



# CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC25001485291

Valid from: Sep.18,2025

Valid until: Sep.17,2030

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** Analog Devices, Inc.  
804 Woburn Street Wilmington MA USA

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** Analog Devices, Inc.  
804 Woburn Street Wilmington MA USA

**NAME AND LOCATION OF THE FACTORY** Analog Devices Gen Trias, Inc  
Sandoval St. Gateway Business Park, Javalera, General Trias, Cavite, Philippines 4107

**PRODUCT NAME, MODEL AND SPECIFICATION** Isolated RS-485  
ADM2561EBRNZ, ADM2563EBRNZ, ADM2565EBRNZ, ADM2567EBRNZ , External creepage distance: 8.3mm, passed 125°C thermal cycle test, Reinforced insulation: maximum working voltage: 415V effective value, 587V peak. Basic insulation: maximum working voltage: 830V effective value, 1174V peak. Dielectric strength voltage: 3000V effective value, 4242V peak. ADM2861EBRNZ, ADM2863EBRNZ, ADM2865EBRNZ, ADM2867EBRNZ , External creepage distance: 8.3mm, passed 125°C thermal cycle test, Reinforced insulation: maximum working voltage: 415V effective value, 587V peak. Basic insulation: maximum working voltage: 830V effective value, 1174V peak. Dielectric strength voltage: 5700V effective value, 8061V peak. (Altitude up to 5000m)

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** GB 4943.1-2022

**TYPE OF CERTIFICATION SCHEMES** Type testing + Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGNATURE:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.  
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666  
<http://www.cqc.com.cn>