



产品认证证书

证书编号: CQC26001508554

发证日期: 2026 年 05 月 21 日
有效期至: 2031 年 05 月 20 日

委托人名称 Analog Devices, Inc.
及注册地址 804 Woburn Street Wilmington MA 美国

制造商名称 Analog Devices, Inc.
及注册地址 804 Woburn Street Wilmington MA 美国

生产企业名称 Analog Devices Gen Trias, Inc
及生产地址 Sandoval St. Gateway Business Park, Javalera, General Trias, Cavite, 菲律宾 4107

产品名称和系列、规格、型号 数字隔离器
ADUM360N0BRWZ, ADUM360N0WBRWZ, ADUM360N1BRWZ, ADUM360N1WBRWZ, ADUM361N0BRWZ, ADUM361N0WBRWZ, ADUM361N1BRWZ, ADUM361N1WBRWZ, ADUM362N0BRWZ, ADUM362N0WBRWZ, ADUM362N1BRWZ, ADUM362N1WBRWZ, ADUM363N0BRWZ, ADUM363N0WBRWZ, ADUM363N1BRWZ, ADUM363N1WBRWZ: 外部爬电距离: 8.0mm, 通过 125°C 热循环测试, 加强绝缘: 最大工作电压: 400V 有效值, 565V 峰值。基本绝缘: 最大工作电压: 800V 有效值, 1131V 峰值。抗电强度试验电压: 5700V 有效值, 8061V 峰值(适用于海拔 5000 米及以下)

产品标准和技术要求 GB 4943.1-2022

认证模式 型式试验+初始工厂检查+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



中国质量认证中心有限公司
中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666
<http://www.cqc.com.cn>



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC26001508554

Valid from: May.21,2026

Valid until: May.20,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT Analog Devices, Inc.
804 Woburn Street Wilmington MA USA

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER Analog Devices, Inc.
804 Woburn Street Wilmington MA USA

NAME AND LOCATION OF THE FACTORY Analog Devices Gen Trias, Inc
Sandoval St. Gateway Business Park, Javalera, General Trias, Cavite, Philippines 4107

PRODUCT NAME, MODEL AND SPECIFICATION Digital Isolator
ADUM360N0BRWZ, ADUM360N0WBRWZ, ADUM360N1BRWZ, ADUM360N1WBRWZ, ADUM361N0BRWZ, ADUM361N0WBRWZ, ADUM361N1BRWZ, ADUM361N1WBRWZ, ADUM362N0BRWZ, ADUM362N0WBRWZ, ADUM362N1BRWZ, ADUM362N1WBRWZ, ADUM363N0BRWZ, ADUM363N0WBRWZ, ADUM363N1BRWZ, ADUM363N1WBRWZ : External creepage distance: 8.0mm, passed 125°C thermal cycle test, Reinforced insulation: maximum working voltage: 400V effective value, 565V peak. Basic insulation: maximum working voltage: 800V effective value, 1131V peak. Dielectric strength voltage: 5700V effective value, 8061V peak. (Altitude up to 5000m)

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB 4943.1-2022

TYPE OF CERTIFICATION SCHEMES Type testing of product + initial factory inspection + follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666
<http://www.cqc.com.cn>