


REV	APPR	DATE
-----	------	------

## NOTES: UNLESS OTHERWISE SPECIFIED:


1. ARTWORK P/N Demo Circuit 1039A
2. FAB PER IPC-A-600. 4-Layers.
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4  
.062 +/- .005 INCH THICKNESS WITH 2 OZ.  
COPPER FINISH ON TWO OUTER LAYERS AND  
2 OZ. COPPER ON TWO INTERNAL LAYERS.  
FLAMABILITY RATING: 94 V-2 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
5. BOARD: SELECTIVE PLATED BOARD. SOLDER  
MASK OVER BARE COPPER, COLOR, GREEN LPI.  
SILKSCREEN COMPONENT SIDE WITH WHITE NON-  
CONDUCTIVE INK.  
WHITE TIN IMMERSION (OMIKRON).  
PLATE THRU ALL HOLES WITH COPPER  
MIN. PLATING THICKNESS: 1 OZ. EXCEPT  
WHERE PLATING NOT REQUIRED
6. DRILL: ALL HOLES SHALL BE DRILLED +/--.003 INCH  
WITH RESPECT TO CTR. OF DRILLED PAD.  
ALL HOLES FINISHED SIZE AFTER PLATING.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING: Applies for production qty's only.



9. DO NOT ALTER SOLDER MASK MAINTAIN .0015 (1.5 MIL) CLEARANCE ON SMT PADS. MUST MAINTAIN ALL WEBBING ON SMD PADS.

## Fabrication Drawing

SIZE	QTY	SYM	PLATED	TOL
190	4	+	YES	+/-0.0
72	2	X	NO	+/-0.0
10	55	□	YES	+/-0.0
35	32	◇	YES	+/-0.0
64	4	⊗	YES	+/-0.0

[illegible]

Linear Tech. Corp.  
Demo Circuit 1039A

## Fabrication Drawing