



Certificate of Compliance

Certificate: 80228929 **Master Contract:** 205078
Project: 80228929 **Date Issued:** 2025-05-06
Issued to: Analog Devices Inc.
804 Woburn St
Wilmington, Massachusetts
01887-3462
United States
Issued by: Martin Buchanan
Martin Buchanan, P. Eng.

Attention: IvyMae Tejero

The products listed below are eligible to bear the CSA Mark shown with adjacent indicator ▲



PRODUCTS

Class 9073 30 ELECTRONIC COMPONENTS - Optoisolators and non-optical isolating devices

Model(s)
ADuM360N0BRQZ, ADuM360N1BRQZ, ADuM361N0BRQZ, ADuM361N1BRQZ, ADuM362N0BRQZ, ADuM362N1BRQZ, ADuM363N0BRQZ, ADuM363N1BRQZ, ADuM360N0WBRQZ, ADuM360N1WBRQZ, ADuM361N0WBRQZ, ADuM361N1WBRQZ, ADuM362N0WBRQZ, ADuM362N1WBRQZ, ADuM363N0WBRQZ, ADuM363N1WBRQZ

Component Acceptance of Optoisolator Like Devices:

Device (QSOP16 RQ-16 package)	Rating		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)



Certificate: 80228929

Master Contract: 205078

Project: 80228929

Date Issued: 2025-05-06

Device (QSOP16 RQ-16 package)	Rating		Standard/Notice and Clauses	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
ADuM360N0BRQZ ADuM360N1BRQZ ADuM361N0BRQZ ADuM361N1BRQZ ADuM362N0BRQZ ADuM362N1BRQZ ADuM363N0BRQZ ADuM363N1BRQZ ADuM360N0WBRQZ ADuM360N1WBRQZ ADuM361N0WBRQZ ADuM361N1WBRQZ ADuM362N0WBRQZ ADuM362N1WBRQZ ADuM363N0WBRQZ ADuM363N1WBRQZ	3.0	125	CSA 62368-1:19, UPD1:2021 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1-12+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1:14 (R2022)+A1+A2 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 IEC 62368-1:2018 Ed. 3 3 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4 61010-1 3 rd Ed+A1 6.7.1.3, 6.7.2.1 or tbK.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1+A2 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 62368-1:2020+A11:2020 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.8, 5.4.1.5.3, 5.4.9.1, 5.4.1.4	-	-	3.5

where Z if used indicates the lead-free version. Suffix EP if present at the end of the base part number indicates lower extended temperature capability to -55C with a NiPdAu lead finish. Further suffix letters or digits differentiate shipping package formats.

Notes:

1. The devices meet basic insulation requirements for 350Vrms and reinforced insulation requirements for 175Vrms for CSA 62368-1:19, UPD1:2021. IEC 62368-1:2018 Ed. 3 and EN62368-1:2020. (pollution degree 2, material group III)
2. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed. the devices meet 300Vrms for basic insulation and 150V for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. The risk management process is not applicable to these clauses. (pollution degree 2, material group III)
3. For CSA 60601-1:14 (R2022) and IEC 60601-1:2005 Ed 3.0+A1+A2 for 1 MOPP for 187Vrms or 2 MOPP for 50Vrms, the devices meet clauses 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.
4. Case material: material group I.
5. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
6. The creepage and clearance has been evaluated for altitudes ≤ 2000m, in pollution degree 2 and overvoltage category II except where specified above. (pollution degree 2, material group III).

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.



Certificate: 80228929

Master Contract: 205078

Project: 80228929

Date Issued: 2025-05-06

APPLICABLE REQUIREMENTS

CSA C22.2 No. 62368-1:19 - Third Edition - Including Update No. 1 October 2021 - Audio/video, information and communication technology equipment — Part 1: Safety requirements

CSA C22.2 No. 61010-1-12, UPD1:2015, UPD2:2016, AMD1:2018 - Safety requirements for electrical equipment for measurement, control, and laboratory use — Part 1: General requirements

CAN/CSA-C22.2 60601-1:14 (R2022) - Medical Electrical Equipment - Part 1: General Requirements for Basic Safety and Essential Performance (Adopted IEC 60601-1:2005, third edition + Amendment 1:2012)

IEC 62368-1:2018 - Audio/video, information and communication technology equipment – Part 1: Safety requirements - Edition 3.0

IEC 61010-1:2010, IEC 61010-1:2010/AMD1:2016 - Amendment 1 - Safety requirements for electrical equipment for measurement, control, and laboratory use - Part 1: General requirements

IEC 60601-1:2005/AMD1:2012/AMD2:2020 - Medical electrical equipment – Part 1: General requirements for basic safety and essential performance - Edition 3.2; Consolidated Reprint; Incorporates Amendment 1: 2012, Corrigenda 1: 12/2012, Corrigenda to Amendment 1: 07/2014, Interpretation 1: 04/2008, Interpretation 2: 01/2009, and Interpretation 3: 05/2013 and Amendment 2: 08/2020

EN 62368-1: 2020/A11:2020 - Audio/video, information and communication technology equipment - Part 1: Safety requirements - Incorporates Amendment A11: 2020



Certificate: 80228929

Project: 80228929

Master Contract: 205078

Date Issued: 2025-05-06

Notes:

Products certified under Class(es) C907330 have been certified under CSA's ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC). www.scc.ca

