

CERTIFICATE OF COMPLIANCE

Certificate Number 20181121-E214100
Report Reference E214100-20160408
Issue Date 2018-NOVEMBER-21

Issued to: ANALOG DEVICES INC
804 WOBURN ST
WILMINGTON MA 01887-3494

This certificate confirms that representative samples of COMPONENT - NONOPTICAL ISOLATING DEVICES
See Addendum for Models

Have been investigated by UL in accordance with the component requirements in the Standard(s) indicated on this Certificate. UL Recognized components are incomplete in certain constructional features or restricted in performance capabilities and are intended for installation in complete equipment submitted for investigation to UL LLC.

Standard(s) for Safety: UL 1577, Optical Isolators
Additional Information: See the UL Online Certifications Directory at <https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Recognized Component Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number 20181121-E214100
Report Reference E214100-20160408
Issue Date 2018-NOVEMBER-21

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Single Protection Non-Optical Isolator, Models ADM2481, ADM2482E, ADM2483, ADM2484E, ADM2485, ADM2486, ADM2487E, ADM2490E, ADM2491E, ADM2582E, ADM2587E, ADM2682E, ADM2687E, ADM3052, ADM3053, ADM3054, ADUM1100, ADUM1200, ADUM1201, ADUM1210, ADuM1220, ADUM1223, ADUM1230, ADUM1233, ADUM1234, ADUM1250, ADUM1251, ADUM1280, ADUM1281, ADUM1285, ADUM1286, ADUM1300, ADUM1301, ADUM1310, ADUM1311, ADUM1400, ADUM1401, ADUM1402, ADUM1410, ADUM1411, ADUM1412, ADUM1510, ADUM2200, ADUM2201, ADUM2210, ADUM2211, ADUM2250, ADUM2251, ADUM2280, ADUM2281, ADUM2285, ADUM2286, ADUM2400, ADUM2401, ADUM2402, ADUM3100, ADUM3150, ADUM3151, ADUM3152, ADUM3153, ADUM3154, ADUM3160, ADUM3200, ADUM3201, ADUM3210, ADUM3211, ADUM3220, ADUM3221, ADUM3223, ADuM3123, ADUM3300, ADUM3301, ADUM3400, ADUM3401, ADUM3402, ADUM3440, ADUM3441, ADUM3442, ADuM4070, ADuM4150, ADuM4151, ADuM4152, ADuM4153, ADuM4154, ADUM4160, ADUM4190, ADUM4223, ADUM4400, ADUM4401, ADUM4402, ADUM4470, ADUM4471, ADUM4472, ADUM4473, ADUM5000, ADuM5020-5BRWZ, ADuM5020-3BRWZ, ADuM5028-5BRIZ, ADuM5028-3BRIZ, ADUM5200, ADUM5201, ADUM5202, ADUM5230, ADUM5240, ADUM5241, ADUM5242, ADUM5400, ADUM5401, ADUM5402, ADUM5403, ADUM5404, ADUM6000, ADuM6020-5BRIZ, ADuM6020-3BRIZ, ADuM6028-5BRIZ, ADuM6028-3BRIZ, ADUM6132, ADUM6200, ADUM6201, ADUM6202, ADUM6400, ADUM6401, ADUM6402, ADUM6403, ADUM6404, ADUM7234, ADUM7240, ADUM7241.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



File E214100
Project 4787329678

April 8, 2016

REPORT

on

COMPONENT - Nonoptical Isolating Devices

ANALOG DEVICES INC
WILMINGTON, MA

Copyright © 2016 UL LLC

UL LLC authorizes the above named company to reproduce this Report only for purposes as described in the Conclusion. The Report should be reproduced in its entirety; however to protect confidential product information, the Construction Details Descriptive pages may be excluded.

DESCRIPTION

PRODUCT COVERED:

USR Single Protection Non-Optical Isolator, Models ADM2481, ADM2482E, ADM2483, ADM2484E, ADM2485, ADM2486, ADM2487E, ADM2490E, ADM2491E, ADM2582E, ADM2587E, ADM2682E, ADM2687E, ADM3052, ADM3053, ADM3054, ADUM1100, ADUM1200, ADUM1201, ADUM1210, ADuM1220, ADUM1223, ADUM1230, ADUM1233, ADUM1234, ADUM1250, ADUM1251, ADUM1280, ADUM1281, ADUM1285, ADUM1286, ADUM1300, ADUM1301, ADUM1310, ADUM1311, ADUM1400, ADUM1401, ADUM1402, ADUM1410, ADUM1411, ADUM1412, ADUM1510, ADUM2200, ADUM2201, ADUM2210, ADUM2211, ADUM2250, ADUM2251, ADUM2280, ADUM2281, ADUM2285, ADUM2286, ADUM2400, ADUM2401, ADUM2402, ADUM3100, ADUM3150, ADUM3151, ADUM3152, ADUM3153, ADUM3154, ADUM3160, ADUM3200, ADUM3201, ADUM3210, ADUM3211, ADUM3220, ADUM3221, ADUM3223, ADuM3123, ADUM3300, ADUM3301, ADUM3400, ADUM3401, ADUM3402, ADUM3440, ADUM3441, ADUM3442, ADuM4070, ADuM4150, ADuM4151, ADuM4152, ADuM4153, ADuM4154, ADUM4160, ADUM4190, ADUM4223, ADUM4400, ADUM4401, ADUM4402, ADUM4470, ADUM4471, ADUM4472, ADUM4473, ADUM5000, **ADuM5020-5BRWZ, ADuM5020-3BRWZ, ADuM5028-5BRIZ, ADuM5028-3BRIZ**, ADUM5200, ADUM5201, ADUM5202, ADUM5230, ADUM5240, ADUM5241, ADUM5242, ADUM5400, ADUM5401, ADUM5402, ADUM5403, ADUM5404, ADUM6000, **ADuM6020-5BRIZ, ADuM6020-3BRIZ, ADuM6028-5BRIZ, ADuM6028-3BRIZ**, ADUM6132, ADUM6200, ADUM6201, ADUM6202, ADUM6400, ADUM6401, ADUM6402, ADUM6403, ADUM6404, ADUM7234, ADUM7240, ADUM7241.

MAXIMUM RATINGS PER CHANNEL (at 25°C ambient) (\$):

Model	Current (mA)		Power (mW)		Isolation Voltage at 60 sec Vrms	Max Operating Ambient Temp (°C)	Max Junction Temp (°C)	Max Storage Temp (°C)	Max Data Rate, Mbps
	Side 1 Transmitter	Side 2 Receiver	Side 1 Transmitter	Side 2 Receiver					
ADM2481	2.5	3.5	12.5	18.5	2500	85	100	150	1
ADM2482E	6.5	70	120	215	2500	105	125	150	16
ADM2483	2.5	3.5	12.5	18.5	2500	85	100	150	1
ADM2484E	6	60	30	230	5000	105	125	150	1
ADM2485	6.5	70	60	230	2500	85	125	150	16
ADM2486	5.4	6.6	24	31	2500	85	100	150	20
ADM2487E	6.5	70	120	215	2500	105	125	150	1
ADM2490E	6	60	30	230	5000	105	125	150	16
ADM2491E	6	60	30	230	5000	105	125	150	16
ADM2582E	150	100	600	500	2500	85	125	150	16
ADM2587E	150	100	600	500	2500	85	125	150	1
ADM2682E	180	55	600	182	5000	85	125	150	16
ADM2687E	140	40	460	132	5000	85	125	150	1
ADM3052	3	75	15	500	5000	85	130	150	1
ADM3053	170	100	850	525	2500	85	130	150	1
ADM3054	3	75	15	375	5000	125	150	150	1
ADUM1100	14	2.8	77	15.4	2500	125	150	150	100
ADUM1200	13	3.4	72	19	2500	125	150	150	25
ADUM1201	8	8	44	44	2500	125	150	150	25
ADUM1210	5.5	2	31	11	2500	125	150	150	10
ADuM1220	7	42	39	506	2500	105	150	150	10
ADUM1223	9	44	50	506	2500	105	150	150	10

MAXIMUM RATINGS PER CHANNEL (at 25°C ambient) (\$): cont.

Model	Current (mA)		Power (mW)		Isolation Voltage at 60 sec Vrms	Max Operating Ambient Temp (°C)	Max Junction Temp (°C)	Max Storage Temp (°C)	Max Data Rate, Mbps
	Side 1 Transmitter	Side 2 Receiver	Side 1 Transmitter	Side 2 Receiver					
ADUM1230	8	44	44	506	2500	105	150	150	10
ADUM1233	9	44	50	506	2500	105	150	150	10
ADUM1234	9	44	50	506	2500	105	150	150	10
ADUM1250	5	5	27.5	27.5	2500	105	150	150	1
ADUM1251	6	4.7	33	26	2500	105	150	150	1
ADUM1280	25	15	138	83	3000	125	150	150	100
ADUM1281	19	19	104	104	3000	125	150	150	100
ADUM1285	25	15	138	83	3000	125	150	150	100
ADUM1286	19	19	104	104	3000	125	150	150	100
ADUM1300	77	18	423	99	2500	125	150	150	90
ADUM1301	57	37	313	203	2500	125	150	150	90
ADUM1310	9	3	50	17	2500	105	150	150	10
ADUM1311	5.7	4.3	32	24	2500	105	150	150	10
ADUM1400	100	25	550	138	2500	125	150	150	90
ADUM1401	82	43	451	236	2500	125	150	150	90
ADUM1402	62	62	341	341	2500	125	150	150	90
ADUM1410	12	4	66	22	2500	105	150	150	10
ADUM1411	7.6	5.3	42	29	2500	105	150	150	10
ADUM1412	6.5	6.5	36	36	2500	105	150	150	10
ADUM1510	12	4.5	66	25	2500	105	150	150	10
ADUM2200	4.6	2.8	25.3	15.4	5000	105	150	150	10
ADUM2201	3.4	4.0	18.7	15.4	5000	105	150	150	10
ADUM2210	4.6	2.8	25.3	15.4	5000	105	150	150	10
ADUM2211	3.4	4.0	18.7	15.4	5000	105	150	150	10
ADUM2250	5	5	27.5	27.5	5000	125	150	150	1
ADUM2251	6	4.7	33	26	5000	125	150	150	1
ADUM2280	25	15	138	83	5000	125	150	150	100
ADUM2281	19	19	104	104	5000	125	150	150	100
ADUM2285	25	15	138	83	5000	125	150	150	100
ADUM2286	19	19	104	104	5000	125	150	150	100
ADUM2400	100	25	550	137	5000	105	150	150	90
ADUM2401	82	43	451	236	5000	105	150	150	90
ADUM2402	62	62	341	341	5000	105	150	150	90
ADUM3100	14	2.8	77	15.4	2500	125	150	150	50
ADUM3150	15	13.5	60	67.5	*3750	125	150	150	40
ADUM3151	14	13.5	55	67.5	*3750	125	150	150	17
ADUM3152	14	14	55	70	*3750	125	150	150	17
ADUM3153	14	13.3	55	66.5	*3750	125	150	150	17
ADUM3154	10	13.5	50	67.5	*3750	125	150	150	17
ADUM3160	8	8	44	44	2500	105	150	150	12
ADUM3200	10	3.9	55	22	2500	125	150	150	25
ADUM3201	6.8	8.3	38	46	2500	125	150	150	25
ADUM3210	4.6	2.8	26	16	2500	125	150	150	10
ADUM3211	3.4	4	19	22	2500	105	150	150	10

MAXIMUM RATINGS PER CHANNEL (at 25°C ambient) (\$): cont.

Model	Current (mA)		Power (mW)		Isolation Voltage at 60 sec Vrms	Max Operating Ambient Temp (°C)	Max Junction Temp (°C)	Max Storage Temp (°C)	Max Data Rate, Mbps
	Side 1 Transmitter	Side 2 Receiver	Side 1 Transmitter	Side 2 Receiver					
ADUM3220	1.7	60	10	1080	2500	105	150	150	1
ADUM3221	1.7	60	10	1080	2500	105	150	150	1
ADuM3123	1.6	25.6	8	460	3000	125	150	150	1
ADUM3223	2.5	60	14	1080	3000	125	150	150	1
ADUM3300	77	18	423	99	2500	125	150	150	90
ADUM3301	57	37	313	203	2500	125	150	150	90
ADUM3400	100	25	550	138	2500	125	150	150	90
ADUM3401	82	43	451	236	2500	125	150	150	90
ADUM3402	44	62	242	341	2500	125	150	150	90
ADUM3440	220	55	1200	302	2500	125	150	150	150
ADUM3441	165	80	907	440	2500	125	150	150	150
ADUM3442	130	130	715	715	2500	125	150	150	150
ADuM4070	5	8.5	35	60	5000	105	150	150	40
ADuM4150	15	13.5	60	67.5	5000	105	150	150	17
ADuM4151	14	13.5	55	67.5	5000	105	150	150	17
ADuM4152	14	14	55	70	5000	105	150	150	17
ADuM4153	14	13.3	55	66.5	5000	105	150	150	17
ADuM4154	10	13.5	50	67.5	5000	105	150	150	17
ADUM4160	8	8	44	44	5000	105	150	150	12
ADUM4190	2	5	40	100	5000	125	150	150	0.4
ADUM4223	2.5	60	14	1080	5000	125	150	150	1
ADUM4400	100	36	550	198	5000	105	150	150	90
ADUM4401	82	46	450	253	5000	105	150	150	90
ADUM4402	62	62	341	341	5000	105	150	150	90
ADUM4470	8.75	11	61	77	5000	105	150	150	25
ADUM4471	8.75	11	61	77	5000	105	150	150	25
ADUM4472	8.75	11	61	77	5000	105	150	150	25
ADUM4473	8.75	11	61	77	5000	105	150	150	25
ADuM5020-5BRWZ	310	100	1550	500	3000	125	150	150	0
ADuM5020-3BRWZ	250	60	1250	200	3000	125	150	150	0
ADuM5028-5BRIZ	310	100	1550	500	3000	125	150	150	0
ADuM5028-3BRIZ	250	60	1250	200	3000	125	150	150	0

*

ADUM5000	290	100	1450	500	2500	105	150	150	0
ADUM5200	290	100	1450	500	2500	105	150	150	0
ADUM5201	290	100	1450	500	2500	105	150	150	25
ADUM5202	290	100	1450	500	2500	105	150	150	25
ADUM5230	200	8.5	1000	128	2500	105	150	150	2
ADUM5240	140	3	688	16.5	2500	105	150	150	1
ADUM5241	140	3	688	16.5	2500	105	150	150	1
ADUM5242	140	3	688	16.5	2500	105	150	150	1
ADUM5400	290	100	1450	500	2500	105	150	150	25
ADUM5401	290	100	1450	500	2500	105	150	150	25
ADUM5402	290	100	1450	500	2500	105	150	150	25
ADUM5403	290	100	1450	500	2500	105	150	150	25
ADUM5404	290	100	1450	500	2500	105	150	150	25

MAXIMUM RATINGS PER CHANNEL (at 25°C ambient) (§): cont.

Model	Current (mA)		Power (mW)		Isolation Voltage at 60 sec Vrms	Max Operating Ambient Temp (°C)	Max Junction Temp (°C)	Max Storage Temp (°C)	Max Data Rate, Mbps
	Side 1 Transmitter	Side 2 Receiver	Side 1 Transmitter	Side 2 Receiver					
ADUM6000	290	100	1450	500	5000	105	150	150	0
ADUM6132	350	22	1750	275	2500	85	150	150	2
ADuM6020-5BRIZ	310	100	1550	500	5000	125	150	150	0
ADuM6020-3BRIZ	250	60	1250	200	5000	125	150	150	0
ADuM6028-5BRIZ	310	100	1550	500	5000	125	150	150	0
ADuM6028-3BRIZ	250	60	1250	200	5000	125	150	150	0
ADUM6200	300	74	1350	370	5000	105	150	150	25
ADUM6201	298	72	1341	360	5000	105	150	150	25
ADUM6202	296	70	1332	350	5000	105	150	150	25
ADUM6400	309	69	1390	345	5000	105	150	150	25
ADUM6401	307	67	1382	335	5000	105	150	150	25
ADUM6402	305	65	1373	325	5000	105	150	150	25
ADUM6403	302	63	1359	315	5000	105	150	150	25
ADUM6404	301	61	1354	305	5000	105	150	150	25
ADUM7234	3	60	6	585	1000	105	150	150	1
ADUM7240	20	3.6	110	20	1000	125	150	150	25
ADUM7241	12	11	66	61	1000	125	150	150	25

(§) - For ambient temperatures higher than 25°C and up to T_{moa}, refer to manufacturer's specifications and/or thermal derating curve data for complete electrical ratings.

GENERAL:

These non-optical isolator devices consist of a transmitter coupled to a receiver. The transmitter and receiver are separated by an [insulating transformer and insulating barrier. Internal chips are connected to lead frames that are molded into the enclosure.

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

Use - For use only in products where the acceptability of the combination is determined by UL LLC.

USR indicates this product was investigated under the UL Standard for Safety for Optical Isolators, UL 1577, Fifth Edition, revised June 11, 2019.

Conditions of Acceptability - Each device shall be reviewed with respect to the following conditions of acceptability:

1. The capability of the device to control a load has not been investigated.
2. These devices should be installed in a suitable end product enclosure.
3. The maximum junction temperature shall not be exceeded.
4. For single protection devices, the insulation to the case has not been evaluated. For double protection devices, the insulation to the case has been evaluated to the isolation voltage specified in the ratings table.
5. In addition to meeting single protection requirements, double protection optical isolators have also been investigated for use in up to 250 V, 50/60 Hz circuits in audio, video, and similar equipment in applications in which breakdown of the optical isolator may result in a risk of fire, electrical shock, or injury to persons.

CONSTRUCTION DETAILS:

General - The product shall be constructed in accordance with the following description. All dimensions are approximate, unless specified as "max" or "min".

Markings - As specified in the Section General.