


NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC)
3. SOLDER MASK : BOTH SIDES USING GREEN LPI
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. ALL DIMENSIONS ARE IN INCHES
6. SCORING:



SIZE	QTY	SYM	PLTD	TOL
72	2	+	NO	+/-0.0
37	16	X	YES	+/-0.0
40	3	⊠	YES	+/-0.0
10	3	◇	YES	+/-0.0
95	4	⊠	YES	+/-0.0

Fabrication Drawing

APPROVALS		INIT		DATE	
DRAWN		KL			
CHECK					
DESIGN					
ENGR					
SCALE = NONE					

LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
Ultralow Quiescent Current, 20mA Linear Regulator			
SIZE	A	DC1156A	REV. A
DEMO BRD		SHT 1 of 1	