




SIZE	QTY	SYM	PLATED	TOL
0.07	2	+	NO	+/-0.003
0.035	3	X	YES	+/-0.003
0.01	61	□	YES	+/-0.003
0.095	7	◇	YES	+/-0.003

NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE 0.062" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS
AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003"
IN RELATION TO CENTER
5. FINISH: -SMBGC USING LPI BOTH SIDES, COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
-LEAD FREE SOLDER CAN BE USED FOR PROTOTYPE)
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE ROHS COMPLIANT.



UNLESS OTHERWISE SPECIFIED	APPROVALS		 LINEAR TECHNOLOGY	1830 MCCARTHY BLVD SUITE 1005 CHICAGO, IL 60642-3900 PH: (408) 432-3900 WWW.LINEAR.COM LITC CONFIDENTIAL - FOR CUSTOMER USE ONLY
	PCB DES.	HZ		
DIMENSIONS ARE IN INCHES	APP ENG.	GEORGE Q.	TITLE: FABRICATION DRAWING	HIGH EFFICIENCY CUK CONVERTER
TOLERANCES:				
0.XXX" = ±0.01"				
0.XXX" = ±0.005"				
INTERPRET DIM AND TOL PER ASME Y14.5M-1994				
THIRD ANGLE PROJECTION				
			SIZE	REV
			N/A	1
	SCALE = NONE		LT3757EDD DEMO CIRCUIT 1548A	
			FILENAME: DC1548A-1PCB	SHT 1 OF 1