


Demo Circuit 1116A

FAB DRAWING




SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-3Mil
63	7	X	YES	+/-3Mil

REVISIONS			
REV	DESCRIPTION	APPR	DATE

NOTES: UNLESS OTHERWISE SPECIFIED.

- ARTWORK P/N Demo Circuit 1116A Rev0
- FAB PER IPC-A-600, 2-Layers.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH AND FLAMABILITY RATING: 94 V-2 MINIMUM .

- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI. WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN BOTH SIDES WITH WHITE NON-CONDUCTIVE INK.
- PLATE THRU ALL HOLES WITH COPPER
- MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/3mil WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



FABRICATION DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE 1°:
3 PLACE .005°
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS			
DRAWN	INIT	DATE	
CHECK			
DESIGN	Rudy Basile	03/04/06	
ENGR	Jon Merson	03/04/06	
SCALE = NONE			

LINEAR TECHNOLOGY

1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE:

Multi-Circuit Current Monitor

SIZE

A

Demo Circuit 1116A

REV.

0

SHT 1 of 1