


EXPOSED COPPER NEAR BOARD EDGES (TOP AND BOTTOM).
(CUT BACK SOLDER MASK, SEE SOLDER MASK DRAWING)




FAB Drawing

SIZE	QTY	SYM	PLTD	TOL
185	4	+	NO	+/-0.003
70	2	X	NO	+/-0.003
31	3	□	YES	+/-0.003
10	40	◇	YES	+/-0.003
94	4	⊗	YES	+/-0.003

- LAYER 1 (COMPONENT SIDE)
■ LAYER 2 (GND)
■ LAYER 3 (GND)
■ LAYER 4 (SOLDER SIDE)

NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY
2 OZ OUTER, 1 OZ INNER COPPER CLAD
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
OR LEAD FREE SOLDER
3. SOLDER MASK OVER BARE COPPER (SMOBC)
4. SILKSCREEN : BOTH SIDES USING GREEN LPI OR EQUIVALENT
5. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
6. SCORING (FOR PRODUCTION RUN)



FAB DRAWING

APPROVALS		INIT		DATE	
DRAWN	CHECK				
DESIGN	ENGR	Antonina K	Victor K	1/24/06	1/24/06
TITLE: LTC3873ETS8 TELECOM DC/DC CONVERTER					
SIZE		A		DC1154A	
REV.		2		SHT 1 of 1	



1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

DC1154A REV. 2

SHT 1 of 1