



REVISIONS		
REV	DESCRIPTION	DATE

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.  
2 OZ. COPPER FINISH ON OUTER LAYERS.  
1 OZ. COPPER FINISH ON INNER LAYERS.  
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS.  
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES TOL: +/-0.010  
0.000 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, .001 INCH THICK MIN. ALL  
HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/--.003  
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.  
IMMERSION GOLD PLATING
6. SILKSCREEN: BOTH SIDES USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE.  
BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH.
8. PCBs ARE TO BE RoHS COMPLIANT.
9. SCORING:




Top Side

Fabrication Drawing

SIZE	QTY	SYM	PLTD	TOL
0.07	2	+	NO	+/-0.003
0.065	4	X	YES	+/-0.003
0.095	9	□	YES	+/-0.003
0.01	38	◇	YES	+/-0.003
0.035	13	⊠	YES	+/-0.003
0.06	4	⊞	YES	+/-0.003

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
TOLERANCES ON ANGLE ± 1  
2 PLACE ±.01 3 PLACE ±.005  
INTERPRET DIM AND TOL  
PER ASME Y14.5M - 1994

APPROVALS		 <b>LINEAR TECHNOLOGY</b> 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	TITLE: LT3572EUF Dual Full-Bridge Piezo Driver with 900mA Boost Converter	
DRAWN	INIT			
CHECK	DATE			
DESIGN	Helen 9/24/07			
ENGR	WEI GU 9/24/07			
		SIZE		REV.
		A	DC1197A	A
SCALE = NONE		DES		SHEET 1 of 1