



REVISIONS			
REV	DESCRIPTION	APPR	DATE



NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600. PCBs ARE TO BE ROHS COMPLIANT.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON OUTER LAYERS.
1 OZ. COPPER FINISH ON INNER LAYERS.
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/--.003
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
GOLD IMMERSION BOTH SIDES. LEAD FREE SOLDER FOR PROTOTYPE.

6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE
BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH.
8. SCORING:



SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-0.003
10	44	X	YES	+/-0.003
35	21	□	YES	+/-0.003
95	9	◇	YES	+/-0.003

FAB DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ± 1
2 PLACE ± .01 3 PLACE ± .005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS		LINEAR TECHNOLOGY	
PCB DESIGNER	DATE	1630 McCarthy Blvd. Milpitas, CA 95035 Phi: (408)432-1900	
J. WU	2/16/07		
ENGINEER			
T. Gross	2/16/07		
CHECK			
		TITLE: LTC3605EUF 5A Monolithic Synchronous Buck Regulator	
		SIZE A	REV. 1
		DC1215A	
SCALE = NONE		SHT 1 of 1	