

1.0 SCOPE

This specification documents the detailed requirements for Analog Devices space qualified die including die qualification as described for Class K in MIL-PRF-38534, Appendix C, Table C-II except as modified herein.

The manufacturing flow described in the STANDARD DIE PRODUCTS PROGRAM brochure at http://www.analog.com/marketSolutions/militaryAerospace/pdf/Die_Broc.pdf is to be considered a part of this specification.

This data sheet specifically details the space grade version of this product. A more detailed operational description and a complete data sheet for commercial product grades can be found at www.analog.com/MAT02

2.0 Part Number. The complete part number(s) of this specification follow:


<u>Part Number</u>	<u>Description</u>
MAT02-000C	Low-Noise Matched Dual Monolithic Transistor

3.0 Die Information

3.1 Die Dimensions

Die Size	Die Thickness	Bond Pad Metalization
56 mil x 60 mil	19 mil \pm 2 mil	Al/Cu

3.2 Die Picture



1. C1
2. B1
3. E1
4. E2
5. B2
6. C2

Substrate can be connected to V- or floated.

ASD0012815

Rev.H

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
Tel: 781.329.4700 www.analog.com
Fax: 781.326.8703 © 2011 Analog Devices, Inc. All rights reserved.

MAT02

3.3 Absolute Maximum Ratings

Collector to Base Voltage (BV_{CBO}).....	40V
Collector to Emitter Voltage (BV_{CEO}).....	40V
Emitter to Emitter Voltage (BV_{EE}).....	40V
Collector Current (I_C)	20mA
Emitter Current (I_E)	20mA
Storage Temperature	-65°C to +150°C
Junction Temperature (T_J).....	+150°C
Operating Ambient Temperature Range.....	-55°C to +125°C

Absolute Maximum Ratings Notes:

- 1/ Stresses above the absolute maximum rating may cause permanent damage to the device. Extended operation at the maximum levels may degrade performance and affect reliability.

4.0 Die Qualification

In accordance with class-K version of MIL-PRF-38534, Appendix C, Table C-II, except as modified herein.

- (a) Qual Sample Size and Qual Acceptance Criteria – 25/2
- (b) Qual Sample Package – 6 Lead TO Package
- (c) Pre-screen electrical test over temperature performed post-assembly prior to die qualification.

Table I - Dice Electrical Characteristics

Parameter	Symbol	Conditions <u>1/</u>	Limit Min	Limit Max	Units
Current Gain	h_{FE}	$V_{CB} = 0V, 40V$	$I_C = 1mA$	500	
			$I_C = 100\mu A$	500	
			$I_C = 10\mu A$	400	
Current Gain Match <u>2/</u>	Δh_{FE}	$I_C = 10\mu A, 100\mu A, 1mA;$ $V_{CB} = 0V$		2	%
Offset Voltage	V_{OS}	$V_{CB} = 0V$		50	μV
Offset Voltage vs. V_{CB}	$\Delta V_{OS} / \Delta V_{CB}$	$V_{CB} = 0V, 40V$		25	μV
Offset Voltage vs. Collector Current	$\Delta V_{OS} / \Delta I_C$	$V_{CB} = 0V; I_C = 10\mu A, 1mA$		25	μV
Input Offset Current	I_{OS}	$V_{CB} = 0V, 40V$		0.6	nA
Offset Current vs. V_{CB}	$\Delta I_{OS} / \Delta V_{CB}$	$V_{CB} = 0V, 40V$		70	pA/V
Bulk Emitter Resistance	r_{BE}			0.5	Ω

Table I - Dice Electrical Characteristics (Continued)

Parameter	Symbol	Conditions <u>1/</u>	Limit Min	Limit Max	Units
Bias Current	I_B	$V_{CB} = 0V, 40V$		25	nA
Collector Saturation Voltage	V_{CESAT}	$I_C = 1mA, I_B = 100\mu A$		0.1	V
Breakdown Voltage	BV_{CEO}	$I_C = 100\mu A$		40	V

Table I Notes:

1/ $V_{CB} = 15V$, $I_C = \pm 10\mu A$, and $T_A = 25^\circ C$, unless otherwise specified.

2/ Current gain match (Δh_{FE}) is defined as $\Delta h_{FE} = \frac{100(\Delta I_B)h_{FE} \text{ min}}{I_C}$.

Table II - Electrical Characteristics for Qual Samples

Parameter	Symbol	Conditions <u>1/</u>	Sub-groups	Limit Min	Limit Max	Units	
Current Gain	h_{FE}	$I_C = 1mA; V_{CB} = 0V, 40V$	1	450			
			2, 3	225			
		$I_C = 100\mu A; V_{CB} = 0V, 40V$	1	450			
			2, 3	$I_C = 100\mu A; V_{CB} = 15V$	175		
				$I_C = 10\mu A; V_{CB} = 0V, 40V$	350		
$I_C = 10\mu A; V_{CB} = 15V$	125						
Current Gain Match <u>2/</u>	Δh_{FE}	$I_C = 10\mu A, 100\mu A, 1mA; V_{CB} = 0V$	1		3	%	
Offset Voltage	V_{OS}	$V_{CB} = 0V$	1		60	μV	
			2, 3		90		
Offset Voltage vs. Temperature <u>4/</u>	TCV_{OS}	$V_{CB} = 0V$			0.4	$\mu V/^{\circ}C$	
Offset Voltage vs. V_{CB}	$\Delta V_{OS} / \Delta V_{CB}$	$V_{CB} = 0V, 40V$	1		40	μV	
Offset Voltage vs. Collector Current	$\Delta V_{OS} / \Delta I_C$	$V_{CB} = 0V; I_C = 10\mu A, 1mA$	1		40	μV	
Input Offset Current	I_{OS}	$V_{CB} = 0V, 40V$	1		1	nA	
			2, 3		10		
Offset Current vs. V_{CB}	$\frac{\Delta I_{OS}}{\Delta V_{CB}}$	$V_{CB} = 0V, 40V$	1		100	pA/V	
Bulk Emitter Resistance	r_{BE}		1		0.75	Ω	
Collector Base Leakage Current	I_{CBO}	$V_{CB} = 40V$	1		200	pA	
Collector Emitter Leakage Current <u>3/</u>	I_{CES}	$V_{CE} = 40V, V_{BE} = 0V$	1		200	pA	
Collector-Collector Leakage Current <u>3/</u>	I_{CC}	$V_{CC} = 40V$	1		200	pA	
Bias Current	I_B	$V_{CB} = 0V, 40V$	1		30	nA	
			2, 3		70		
Collector Saturation Voltage	V_{CESAT}	$I_C = 1mA, I_B = 100\mu A$	1		0.1	V	
Breakdown Voltage	BV_{CEO}	$I_C = 100\mu A$	1	40			

Table II Notes:

1/ $V_{CB} = 15V, I_C = \pm 10\mu A$, and $T_A = 25^{\circ}C$, unless otherwise specified.

2/ Current gain match (Δh_{FE}) is defined as: $\Delta h_{FE} = \frac{100(\Delta I_B)h_{FE} \text{ min}}{I_C}$.

3/ I_{CC} and I_{CES} are verified by measurement of I_{CBO} .

4/ Guaranteed by V_{OS} test ($TCV_{OS} \cong \frac{V_{OS}}{V_{BE}}$ for $V_{OS} \ll V_{BE}$) $T=298^{\circ}K$ for $T_A=+25^{\circ}C$.

Table III - Life Test Endpoint and Delta Parameter
 (Product is tested in accordance with Table II with the following exceptions)

Parameter	Symbol	Sub-groups	Post Burn In Limit		Post Life Test Limit		Life Test Delta	Units
			Min	Max	Min	Max		
Current Gain @ 1mA	h _{FE}	1	370		290		±80	
		2, 3			145			
Current Gain @ 100µA	h _{FE}	1	360		270		±90	
		2, 3			135			
Current Gain @ 10µA	h _{FE}	1	250		150		±100	
		2, 3			75			
Input Offset Current	I _{OS}	1		1.5		2	±0.5	nA
		2, 3				11.5		

5.0 Life Test/Burn-In Information

- 5.1 HTRB is not applicable for this drawing.
- 5.2 Burn-in is per MIL-STD-883 Method 1015 test condition A, B, or C.
- 5.3 Steady state life test is per MIL-STD-883 Method 1005.

Rev	Description of Change	Date
A	Initiate	Feb. 28, 2002
B	Update web address	Aug. 5, 2003
C	Change Pin 4 from C2 to E2 and Pin 6 from E2 to C2	Oct. 15, 2004
D	Update 1.0 Scope description.	Aug. 2, 2007
E	Update header/footer & add to 1.0 Scope description	Feb. 19, 2008
F	Add Junction Temperature(T _J)....150°C to 3.3 Absolute Max Ratings	March 31, 2008
G	Updated Section 4.0c note to indicate pre-screen temp testing being performed.	6-JUN-2009
H	Updated fonts and sizes to ADI standards	7-Oct-2011