Precision Analog Microcontroller, 12-Bit Analog Input/Output with Arm Cortex-M3

FEATURES

- Analog input and output
  - Multichannel, 12-bit, 2MSPS ADC
    - Up to 16 external channels
    - Power, VDAC, and temperature monitor internal channels
    - Single-ended, differential mode
    - 0V to V_{REF} analog input range
    - Input buffer included
    - Digital comparators
- Four 12-bit voltage output VDACs
  - 4-channel, selectable output range
    - 0V to 2.5V or AVDD – 0.1V, 10mA source/sink ability, voltage monitoring
- Four voltage comparators with adjustable hysteresis voltage
- Microcontroller
  - 32-bit Arm Cortex-M3 core, 32-bit RISC architecture
  - Serial wire port supports code download and debug
- Clocking options
  - 16MHz on-chip oscillator
  - 80MHz PLL output
  - External clock source
- Memory
  - Up to 1 MB independent flash/EE memories
  - 48kB SRAM with ECC
  - Support SPI flash mode for optical DSP firmware
- Software triggered, in circuit reprogrammability via I^2C
- On-chip peripherals
  - 1× UART, 2× SPI, 2× I^2C serial input and output
  - GPIO with multilevel voltage (3.3V, 1.8V, and 1.2V) digital inputs
  - 3× 16-bit and 1× 32-bit general-purpose timers
  - Watchdog timers (WDT)
  - 32-element PLA
  - All GPIOs support external interrupt
- Power
  - Multiple supplies
  - AVDD, IOVDDx, and DVDD = 2.85V to 3.63V
  - Flexible operating modes for low-power applications
- Packages and temperature range
  - 4mm × 4mm, 0.4mm pitch, 72-ball CSP_BGA
  - Fully specified for T_J = –40°C to +125°C
- Tools
  - Low-cost QuickStart development system and full third-party support

APPLICATIONS

- Optical networking 100G/200G/400G and higher frequency modules

GENERAL DESCRIPTION

The ADuCM436 is fully integrated, single package device that includes high performance analog peripherals together with digital peripherals controlled by an 80MHz Arm® Cortex®-M3 processor and with integrated flash memories for code and data.

The analog-to-digital converter (ADC) on the ADuCM436 provides 12-bit, 2MSPS data acquisition for up to 16 input pins that can be programmed for single-ended or differential operation with up to four analog comparators. Additionally, the die temperature and supply voltages can be measured.

The ADC input voltage is 0V to V_{REF}. V_{REF} is typically 2.52V. A sequencer is provided that allows a user to select a set of ADC channels to be measured in sequence without software involvement during the sequence. The sequence can optionally repeat automatically at a user selectable rate.

The ADuCM436 support up to four 12-bit voltage DAC outputs (VDACs). Channel 0 to Channel 3 of the ADuCM436 VDAC support a positive voltage range of 0V to 2.5V. This range can be extended to 0V to AVDD. The on-chip buffers on each channel can source 10mA with a maximum 200pF capacitive load.

The ADuCM436 can be configured with digital and analog outputs retaining their output voltages through a watchdog or software reset sequence. Therefore, a product can remain functional even while the device is resetting itself.

The ADuCM436 has a low-power Arm Cortex-M3 processor and a 32-bit reduced instruction set computer (RISC) machine that offer up to 100MIPS peak performance. In addition, integrated within the ADuCM436 are up to 1MB flash memories and 48kB SRAM. The flash memory of the ADuCM436 has two separate 512kB blocks. These two flash memory blocks can also work in SPI flash mode. In this mode, the blocks can be accessed by an SPI host, such as an optical digital signal processor (DSP), with GPIO P2.4 to P2.7.

Note that throughout this data sheet, multifunction pins, such as VDACP0/P5.0, are referred to either by the entire pin name or by a single function of the pin, for example, VDACP0, when only that function is relevant.

For more information about the ADuCM436, contact InfoOpticalNetwork@analog.com.

One Analog Way, Wilmington, MA 01887-2356, U.S.A. | Tel: 781.935.5565 |
©2026 Analog Devices, Inc. All rights reserved.

NOTES

Legal Terms and Conditions
Information furnished by Analog Devices is believed to be accurate and reliable "as is". However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners. All Analog Devices products contained herein are subject to release and availability.