

SELECTED ITEM DRAWING



7 GHz to 13.5 GHz,
Low Noise Amplifier

Unless otherwise
specified
DIMENSIONS
ARE IN INCHES
(MM)

TOLERANCES:
.XX +/- 0.010
.XXX +/- 0.005
.XXXX +/- 0.002
ANGLES +/- .5 DEG

Drawing
practices
per ASME
Y14.100

SIZE
A

DRAWING NUMBER
SID000012

SID000012 Rev. A
Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.

One Analog Way, Wilmington, MA 01887-2356, U.S.A.
Tel: 781.935.5565 www.analog.com
Tel: 800.262.5643 © 2024 Analog Devices, Inc. All rights reserved.

1. SCOPE

1.1. Scope

This drawing establishes the requirements for the 7 GHz to 13.5 GHz, GaAs, PHEMT, MMIC, Low Noise Amplifier, to be screened in accordance with MIL-PRF-38534, Class K, to the requirements specified in 4.1, and 4.2 herein.

1.2. Analog Devices Part Number

Generic Part Number

ADH564S

Screened Part Number

HMC6578

2. APPLICABLE DOCUMENTS

2.1. Government Documents

Unless otherwise specified, the following drawings and standards, of the issue in effect on the date of the accepted purchase order, in the Department of Defense Index of Specifications and Standards (DODISS) and supplement thereto, shall form a part of this drawing to the extent specified herein.

DEPARTMENT OF DEFENSE TEST METHOD STANDARD

MIL-STD-883 Microcircuits

DEPARTMENT OF DEFENSE PERFORMANCE SPECIFICATIONS

MIL-PRF-38534 Hybrid Microcircuits, General Specifications For

MIL-PRF-38535 Integrated Circuit (Microcircuits) Manufacturing, General Specifications For

2.2. Non-Government Documents

The following documents, of the issue in effect on the date of the purchase order, form a part of this drawing to the extent specified herein:

Analog Devices Inc.

HMC564 Data Sheet Commercial Product Die Datasheet v02.0618 (Reference Only)

3. REQUIREMENTS

3.1. General Requirements

The devices delivered shall comply to this specification.

3.2. Design Construction and Physical Dimensions

The design construction and physical dimensions shall be as defined in Figure 1 herein.

3.3. Traceability

Each delivered device shall be traceable to the wafer number and the wafer lot number of each device. Inspection lot records shall be maintained to provide traceability to the specific wafer and wafer lot from which the chips originated.

3.4. Burn-In and Life Test Circuit

The burn-in and life test circuit and conditions shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in test methods 1005 and 1015 per MIL-STD-883.

4. QUALITY ASSURANCE PROVISIONS

4.1. Wafer Acceptance Testing

The wafer lot acceptance testing shall consist of Class Level S inspections per MIL-STD-883 TM 5007. All deliverable Die shall have passed 100% element electrical test per 4.2.1. Element evaluation per 4.2.2 and passed 100% visual inspection, per MIL-STD-883 TM2010 Condition A, after wafer dicing.

4.2. Dice Qualification Requirements

Dice qualification requirements shall be in accordance with MIL-PRF-38534, Appendix C, Table C-II, per Class K.

4.2.1. Element Electrical Test (RF-On Wafer)

Electrical tests shall consist of the tests specified on Table I, tested at room temperature only.

4.2.2. Element Evaluation (Lot Acceptance Testing)

Sample Die shall be randomly selected from the wafer that has successfully passed RF-On wafer testing per 4.2.1 and shall be mounted to suitable fixturing for screening.

4.2.2.1. Initial Electrical Test (Pre Burn-In)

Pre Burn-In electrical tests shall consist of the tests specified on Table II, tested at room temperature only.

4.2.2.2. Interim Electrical Test (Post Burn-In)

Post Burn-In electrical tests shall consist of the tests specified on Table II, tested at room temperature only and shall meet performance requirements in accordance with Table II and Table III.

4.2.2.3. Final Electrical Test (Post Life Test)

Final electrical tests shall consist of the tests specified in Table I, tested at -55 °C and +85 °C, and shall meet performance requirements in accordance with Table II and Table III.

5. MIL-PRF-38534 EXCEPTIONS

5.1. Wafer Fabrication

Foundry information is available upon request.

5.2. Microcircuit Dice Evaluation Requirements (TABLE C-II)

- Pre-screen test post assembly required to Die qualification to remove all assembly related rejects.
- Subgroup 4: mechanical shock or constant acceleration not performed.
- Subgroup 4: Interim and post burn-in electrical tests will include tests screened at +25 °C only.

6. PREPARATION FOR DELIVERY

The preparation for delivery, packaging, preservation, ESD protection and handling shall be in accordance with MIL-PRF-38534.

6.1. Die Packaging Information

The Die shall be delivered in accordance with Table IV herein.

6.2. Inspection Data Requirements

The following data shall accompany each shipment.

- a. A Certificate of Conformance (C of C) certifies that the lot(s) meets all requirements of this specification.
- b. Die Photograph
- c. Attribute data for all tests.
- d. Wafer Lot Acceptance data including photos from SEM inspection in 4.1.
- e. Summary of RF-On wafer test data per 4.2.1.
- f. Element Evaluation test results per 4.2.2.
 - a. Variables data for electrical end-point measurements.
- g. Failure Analysis with photos (If applicable)
- h. A cover sheet indicating the following purchasing information:
 1. Customer purchase order number.
 2. Analog Devices part number.
 3. Part lot identification codes.
 4. Date & quantity shipped.

TABLE I: DIE ELECTRICAL CHARACTERISTICS

Parameter	Conditions <u>1/2/3/</u> Unless otherwise specified	Limits			Units
		Min	Typ	Max	
Gain		16	17	20	dB
Input Return Loss		10	13		dB
Output Return Loss		10	13		dB
Noise Figure			1.8	2.2	dB
Output Power for 1 dB Compression (OP1dB)		9	11		dBm
Output Third Order Intercept Point (OIP3) <u>4/</u>		22	24		dBm
Supply Current (Idd)	No Signal at RFIN		60	70	mA

TABLE I Notes:

1/ Test limits apply at +25 °C only with Vdd1 = Vdd2 = +3.5 V.

2/ RFIN power shall be -10 dBm for all tests unless otherwise noted.

3/ Measurements made at 10 GHz, 11.75 GHz, and 13.5 GHz unless otherwise noted.

4/ Two tone Input Power = -15 dBm each tone with 1 MHz spacing.

TABLE II: ELECTRICAL CHARACTERISTICS FOR QUALIFICATION SAMPLES

Parameter	Conditions <u>1/2/3/5/</u> Unless otherwise specified	Sub-Group	Limits			Units
			Min	Typ	Max	
Gain		4, 5, 6	16	17	20	dB
Input Return Loss		4, 5, 6	10	13		dB
Output Return Loss		4, 5, 6	9	13		dB
Noise Figure		4, 5, 6		1.8	3	dB
Output Power for 1 dB Compression (OP1dB)		4, 5, 6	8	11		dBm
Output Third Order Intercept Point (OIP3) <u>4/</u>		4, 5, 6	20	24		dBm
Supply Current (Idd)	No Signal at RFIN	1, 2, 3		60	80	mA

TABLE II Notes:

1/ Limits apply between -55 °C and +85 °C with Vdd1 = Vdd2 = +3.5 V.

2/ RFIN power shall be -10 dBm for all tests unless otherwise noted.

3/ Measurements made at 10 GHz, 11.75 GHz, and 13.5 GHz unless otherwise noted.

4/ Two tone Input Power = -15 dBm each tone with 1 MHz spacing.

5/ See MIL-PRF-38535 Table C-Xa for subgroup parameter definitions.

TABLE III: BURN-IN/LIFE TEST DELTA LIMITS 1/2/3/


Parameter	Test Conditions	Delta Limits	Units
Gain	Per Table II	± 1	dB
Supply Current (I _{dd})		± 10	%

TABLE III Notes:

1/ Delta test is performed at T_A = +25 °C only.

2/ Table II limits will not be exceeded.

3/ Delta calculated pre/post 240 hours and post 240 hours / post 1000 hours.



PAD	DESCRIPTION	PAD SIZE
1	RFIN	.0039[.100] X .0089[.226]
2, 3	Vdd	.0039[.100] X .0039[.100]
4	RFOUT	.0039[.100] X .0039[.100]

NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MM]
2. DIE THICKNESS IS .004"
3. TYPICAL BOND PAD IS .004" SQUARE
4. BOND PAD METALIZATION: GOLD
5. BACKSIDE METALIZATION: GOLD
6. OVERALL DIE SIZE $\pm .002$ "

Figure 1 – Device Outline for the HMC6578

TABLE IV: DIE PACKAGING INFORMATION

Standard Package	Alternate
GP-2 (Gel Pack)	<u>1</u> /

TABLE IV Note:

1/ For alternate packaging information, contact Analog Devices Inc.

ORDERING GUIDE

Model	Temperature Range
HMC6578	–55 °C to +85 °C

Revision History

Revision History		
Rev	Description of Change	Date
A	Initial release.	10/04/2024