

SELECTED ITEM DRAWING

			
Unless otherwise specified DIMENSIONS ARE IN INCHES (MM)	TOLERANCES: .XX +/- 0.010 .XXX +/- 0.005 .XXXX +/- 0.002 ANGLES +/- .5 DEG	Drawing practices per ASME Y14.100	1.8 GHz to 5 GHz, Double Balanced Mixer
			DRAWING NUMBER SID000085
		SIZE A	

SID000085

Rev. B

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.

One Analog Way, Wilmington, MA 01887-2356, U.S.A.

Tel: 781.935.5565

Fax: 800.262.5643

www.analog.com

© 2025 Analog Devices, Inc. All rights reserved.

1. SCOPE

1.1. Scope

This drawing establishes the requirements for the 1.8 GHz to 5 GHz, GaAs, MMIC, Double-Balanced Mixer, assembled hermetically in the G8 package, to be screened in accordance with MIL-PRF-38535, Class Level S, to the requirements specified in 4.1, 4.2, and 4.3 herein.

1.2. Analog Devices Part Number

<u>Generic Part Number</u>	<u>Screened Part Number</u>
ADH128S	HMC8482G8

2. APPLICABLE DOCUMENTS

2.1. Government Documents

Unless otherwise specified, the following drawings and standards, of the issue in effect on the date of the accepted purchase order, in the Department of Defense Index of Specifications and Standards (DODISS) and supplement thereto, shall form a part of this drawing to the extent specified herein.

DEPARTMENT OF DEFENSE TEST METHOD STANDARD

MIL-STD-883 Microcircuits

DEPARTMENT OF DEFENSE PERFORMANCE SPECIFICATIONS

MIL-PRF-38535 Integrated Circuits (Microcircuits) Manufacturing, General Specification For

2.2. Non-Government Documents

The following documents, of the issue in effect on the date of the purchase order, form a part of this drawing to the extent specified herein:

Analog Devices Inc.

[ADI Standard Space Products Program](#) – *ASD-Lite*.

HMC128G8 Data Sheet Commercial Product Datasheet v02.1105 (Reference Only)

3. REQUIREMENTS

3.1. General Requirements

The devices delivered shall comply to this specification.

3.2. Design Construction and Physical Dimensions

The design construction and physical dimensions shall be as defined in Figure 1 herein.

3.3. Traceability

Each delivered device shall be traceable to the wafer lot and wafer number. Inspection lot records shall be maintained to provide traceability to the specific wafer and wafer lot from which the chips originated as well as traceability to package and materials.

3.4. Burn-In and Life Test Circuit

The burn-in and life test circuit and conditions shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in test methods 1005 and 1015 per MIL-STD-883.

4. QUALITY ASSURANCE PROVISIONS

4.1. Wafer Lot Acceptance Testing

The wafer lot acceptance testing shall consist of Class Level S inspections per MIL-STD-883 TM 5007.

4.2. Flight Screening Requirements

Flight screening requirements shall be per MIL-STD-883 TM 5004 for Class level S microcircuits.

4.2.1. Electrical Test Requirements

Electrical test requirements are defined in Table I herein.

4.2.2. Electrical Performance Characteristics

Electrical performance characteristics are specified on Table II herein.

4.2.3. Burn-In Delta Requirements

Pre and Post Burn-In Electrical test and delta parameters shall consist of the tests specified in Table III herein.

4.3. Quality Conformance Inspection (QCI)

Group B and Group D tests shall be performed per MIL-STD-883 TM 5005 for Class level S microcircuits.

4.3.1. Post Steady State Life Electrical Test

Post steady state life electrical tests shall consist of the tests specified per Table II tested at room temperature only. Devices must meet delta parameter requirements in accordance with Table III herein.

5. MIL-PRF-38535 ASD-LITE EXCEPTIONS

The manufacturing flow described in the ADI STANDARD SPACE PRODUCTS PROGRAM is to be considered a part of this specification.

5.1. Wafer Fabrication

Foundry information is available upon request.

5.2. Flight Screening Flow

Reverse Bias Burn-In: Not applicable.

5.3. Group B

Subgroup 2: Resistance to solvents is not applicable.

Subgroup 2: Not performed.

Subgroup 5: Qty/Acc = 22/0.

Subgroup 5: Life test duration = 2000 Hours.

Subgroup 5: Post life electrical test performed at -40 °C, +25 °C, and +85 °C.

Subgroup 6: Qty/Acc = 3/0.

5.4. Group D

Subgroup 5: Not applicable.

Subgroup 8: Not applicable.

Subgroup 9: Not applicable.

6. PREPARATION FOR DELIVERY

The preparation for delivery, packaging, preservation, ESD protection and handling shall be in accordance with MIL-PRF-38535.

6.1. Part Marking

Devices shall be marked as specified on Figure 1 herein.

6.2. Inspection Data Requirements

The following data shall accompany each shipment.

- a. A Certificate of Conformance (C of C) certifies that the lot(s) meets all requirements of this specification.
- b. Wafer Lot Acceptance data including photos from SEM Inspection defined in 4.1 herein.
- c. Summary of electrical test requirements defined in 4.2 herein.
- d. Summary of QCI results defined in 4.3 herein.
- e. Failure Analysis with photos (If applicable).
- f. A cover sheet indicating the following purchasing information:
 1. Customer purchase order number.
 2. Analog Devices part number.
 3. Part lot identification codes.
 4. Date & quantity shipped.

TABLE I: ELECTRICAL TEST REQUIREMENTS

Test Requirement	Subgroups (in accordance with MIL-PRF-38535, Table III)
Interim Electrical Parameters	4
Final Electrical Parameters	4 <u>1/2/</u>
Group A Electrical Parameters	4, 5, 6
Group B End-Point Electrical Parameters	4 <u>2/</u>
Group D End-Point Electrical Parameters	4

TABLE I Notes:

1/ PDA applies to Table I subgroup 1 and Table III delta parameters.

2/ See Table III for delta parameters.

TABLE II: ELECTRICAL PERFORMANCE CHARACTERISTICS (-40 °C, +25 °C AND +85 °C)

Parameter	Test Conditions <u>1/2/3/</u> Unless otherwise specified	Group A Subgroups	Limits			Units
			Min	Typ	Max	
Conversion Loss	F _{RF} = 2.2 GHz and F _{LO} = 2.07 GHz	4, 5, 6		10	12	dB
Noise Figure (SSB) <u>4/</u>		4, 5, 6		10	12	dB
LO to RF Isolation		4, 5, 6	28	40		dB
LO to IF Isolation		4, 5, 6	20	30		dB
IP3 (Input) <u>5/</u>		4, 5, 6	13	18		dBm
IP2 (Input) <u>4/</u>		4, 5, 6	35	40		dBm
1 dB Gain Compression (Input) <u>5/</u>		4, 5, 6	5	10		dBm

TABLE II Notes:

1/ Test limits between -40 °C and +85 °C.

2/ Measured with P_{RF} = -10 dBm, F_{IF} = 130 MHz, and P_{LO} = +15 dBm.

3/ Typical electrical characteristics may be guaranteed in lieu of testing.

4/ Guaranteed by design and will not be tested.

5/ To be performed on a 5-piece sample from the Life test units.

TABLE III: BURN-IN/LIFE TEST DELTA LIMITS 1/2/3/


Parameter	Test Conditions	Delta Limits	Units
Conversion Loss	Per Table II	± 1	dB

TABLE III Notes:

1/ Delta test is performed at T_A = +25 °C only.

2/ Table II limits will not be exceeded.

3/ Deltas calculated at pre/post 240 hours and post 240 hours / post2000 hours.



NOTES:

1. PACKAGE MATERIAL: ALUMINA LOADED BOROSILICATE GLASS.
2. LEADS, BASE, COVER MATERIAL: KOVAR™ (#7052 CORNING).
4. PLATING: ELECTROLYTIC GOLD 50 MICROINCHES MIN., OVER ELECTROLYTIC NICKEL 50 MICROINCHES MIN.
5. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
6. TOLERANCES: ±.005 [0.13] UNLESS OTHERWISE SPECIFIED.
7. CHARACTERS TO BE LASER MARKED WITH .018"MIN to .030"MAX HEIGHT REQUIREMENTS. UTILIZE MAXIMUM CHARACTER HEIGHT BASED ON LID DIMENSIONS AND BEST FIT. LOCATE APPROX. AS SHOWN.
8. ALL GROUND LEADS AND GROUND PADDLE MUST BE SOLDERED TO PCB RF GROUND.

PIN #	FUNCTION
1	RF
2	GND
3	GND
4	GND
5	IF
6	GND
7	GND
8	LO

Average Weight: 0.13 grams

Figure 1 – Device Outline for the HMC8482G8

ORDERING GUIDE

Model	Temperature Range	Package Description	Package Option
HMC8482G8	-40 °C to +85 °C	8-Lead Glass/Metal Hermetic SMT	G8 (FR-8-2)

Revision History

Revision History		
Rev	Description of Change	Date
A	Initial release	04/16/2025
B	Updated Section 4.3.1 and Figure 1	09/12/2025