

# 12-Bit, Current Output, Complete High Speed D/A Converter

**AD565** 

#### 1.0 **SCOPE**

This specification documents the detailed requirements for Analog Devices space qualified die including die qualification as described for Class K in MIL-PRF-38534, Appendix C, Table C-II except as modified herein.

The manufacturing flow described in the STANDARD DIE PRODUCTS PROGRAM brochure at <a href="http://www.analog.com/aerospace">http://www.analog.com/aerospace</a> is to be considered a part of this specification.

This data sheet specifically details the space grade version of this product. A more detailed operational description and a complete data sheet for commercial product grades can be found at <a href="https://www.analog.com/AD565">www.analog.com/AD565</a>

**2.0 Part Number**. The complete part number(s) of this specification follow:

Part Number Description


AD565-000C 12-Bit, Current Output, Complete High Speed D/A Converter

#### 3.0 <u>Die Information</u>


#### 3.1 <u>Die Dimensions</u>

Die Size	Die Thickness mil	Bond Pad Metalization
119 mil x 146 mil	19 mil ± 2 mil	AI/Cu

#### 3.2 Die Picture



ASD0012329 Rev. G
Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.



## **AD565**

#### 3.3 Absolute Maximum Ratings. 1/

V <sub>CC</sub> to power ground	0 to +18V dc
V <sub>EE</sub> to power ground	0 to -18V dc
Voltage on DAC output (pin 9)	3V dc to +12V dc
Digital inputs (pins 13 to 24) to power ground	1.0V dc to +7.0V dc
Ref in to ref ground	±12V dc
Bipolar offset to reference ground	±12V dc
10V span R to reference ground	±12V dc
20V span R to reference ground	±24V dc
Ref out	
	momentary short to V <sub>CC</sub>
Power dissipation	1000 mW
Storage temperature range	65°C to +150°C
Operating temperature range	55°C to +125°C
Junction temperature (T <sub>J</sub> )	

<sup>1/</sup> Stresses above the absolute maximum rating may cause permanent damage to the device. Extended operation at the maximum levels may degrade performance and affect reliability.

#### 3.4 Recommended operating conditions.

Positive supply voltage (V <sub>CC</sub> )	+15V
Negative supply voltage (V <sub>EE</sub> )	15V
Operating ambient temperature range	55°C to +125°C

### 4.0 <u>Die Qualification</u>

In accordance with class-K version of MIL-PRF-38534, Appendix C, Table C-II, except as modified herein.

- (a) Qual Sample Package Sidebrazed DIP
- (b) Qual Sample Size and Qual Acceptance Criteria 10/0
- (c) Pre-screen electrical test over temperature performed post-assembly prior to die qualification.

#### 5.0 **Dice Electrical Characteristics**

Table I						
Parameter	Symbol	Conditions Limit Note 1 Min		Limit Max	Units	
Relative Accuracy	RA	All bits w/ positive errors on All bits w/ negative errors on		±0.5	LSB	
Differential Nonlinearity	DNL	Major transition		±0.75	LSB	
Gain Error	AE	$R_{REF} = 50 \cdot fixed$		±0.25	% of FS	
Offset Error	Vos			±0.05	% of FS	
Bipolar Zero Error Note 2	B <sub>PZE</sub>	R <sub>BO</sub> = 50• fixed		±0.15	% of FS	
Reference Output Voltage	V <sub>REF</sub>	Note 3	9.90	10.10	V	
Output Current	Іоит —	Unipolar (all bits on)	-1.6	-2.4	mA	
Output Current		Bipolar (all bits on)	-0.8	-1.2	IIIA	
Power Supply Rejection Ratio	PSRR -	$V_S = +11.4V \text{ to } +16.5V \text{ dc}$		±10.0	PPM of FRS/%	
rower supply nejection natio	Pann	$V_S = -11.4V \text{ to } -16.5V \text{ dc}$		±25.0	PPINI OI FN3/90	
Power Supply Current	Icc			+5.0	mA	
Note 4, 5	I <sub>EE</sub>			-18.0	IIIA	
Power Dissipation	PD			345.0	mW	
Digital Input High Voltage	ViH		2.0	5.5	V	
Digital Input Low Voltage	VIL			0.8	V	
Digital Input High Current	I <sub>IH</sub>	V <sub>IH</sub> = 5.5V		300.0	μΑ	
Digital Input Low Current	I <sub>IL</sub>	V <sub>IL</sub> = 0V		100.0	μΑ	

#### Table I Notes:

- 1.  $V_{CC} = +15V$ ,  $V_{EE} = -15V$ ,  $V_{IH} = 2.0V$ ,  $V_{IL} = 0.8V$ ,  $T_A = 25^{\circ}C$ .
- MSB on, all other bits off.
- 3. The reference output is loaded with 0.5mA reference input current, 1.0mA bipolar offset current, and 1.5mA additional current.
- Guaranteed for +11.4 ≤ V<sub>CC</sub> ≤ +16.5V.
   Guaranteed for -11.4 ≤ V<sub>EE</sub> ≤ -16.5V.

#### **Electrical Characteristics for Qual Samples** 5.1

Table II							
Parameter	Symbol	Conditions Note 1	Sub- groups	Limit Min	Limit Max	Units	
Relative Accuracy	RA All bits w/ positive errors on All bits w/ negative errors on		1		±0.5	LSB	
			2, 3		±0.75		
Differential Nonlinearity	DNL	Major transition	1		±0.75	LSB	
,		<u>,                                      </u>	2, 3		±1.0		
Gain Error	AE	R <sub>REF</sub> = 50• fixed	1		±0.25	% of FS	
Gain Error Temperature Coefficient	TCA <sub>E</sub>		2, 3		±30.0	ppm of FS/°C	
Offset Error	Vos		1		±0.05	% of FS	
Offset Error Temperature Coefficient	TCVos		2, 3		±2.0	ppm of FS/°C	
Bipolar Zero Error Note 2	B <sub>PZE</sub>	R <sub>BO</sub> = 50• fixed	1		±0.15	% of FS	
Bipolar Zero Error Temperature Coefficient Note 2	TCB <sub>PZE</sub>		2, 3		±10.0	ppm of FS/°C	
Reference Output Voltage Note 3	$V_{REF}$		1, 2, 3	9.90	10.10	V	
Reference Output Current Note 4	I <sub>REF</sub>		1	1.5		mA	
Outrout Company	,	Unipolar (all bits on)		-1.6	-2.4	0	
Output Current	<b>І</b> оит	Bipolar (all bits on)	1 1	-0.8	-1.2	mA	
Power Supply Rejection Ratio	PSRR	$V_S = +11.4V \text{ to } +16.5V \text{ dc}$	1		±10.0	PPM of FRS/%	
rower supply nejection natio	FJIII	$V_S = -11.4V \text{ to } -16.5V \text{ dc}$			±25.0	- FFWIOITINS/70	
Power Supply Current	lcc .		1		+5.0	mA .	
Note 4, 5	I <sub>EE</sub>				-18.0		
Power Dissipation	P <sub>D</sub>		1		345.0	mW	
Digital Input High Voltage	V <sub>IH</sub>		1	2.0	5.5	V	
Digital Input Low Voltage	V <sub>IL</sub>		1		0.8	V	
Digital Input High Current	I <sub>IH</sub>	V <sub>H</sub> = 5.5V	1		300.0	μΑ	
Digital Input Low Current	IιL	$V_{IL} = 0V$	1		100.0	μΑ	

Table II Notes:

V<sub>CC</sub> = +15V, V<sub>EE</sub> = -15V, V<sub>IH</sub> = 2.0V, V<sub>IL</sub> = 0.8V.
 MSB on, all other bits off.
 In subgroup 1, the reference output is loaded with 0.5mA reference input current, 1.0mA bipolar offset current, and 1.5mA additional current. In subgroup 2 and 3, only the 0.5mA reference input current is applied. The reference must be buffered to supply external loads at elevated temperatures.

Guaranteed for +11.4  $\leq$  V<sub>CC</sub>  $\leq$  +16.5V.

Guaranteed for -11.4  $\leq$  V<sub>EE</sub>  $\leq$  -16.5V.

#### 6.0 <u>Delta Parameter Table</u>

Table III								
Downstan	6	Sub-	Post Burn In Limit		Post Life	Post Life Test Limit		11
Parameter	Symbol	groups	Min	Max	Min	Max	Delta	Units
Gain Error	AE	1		±0.25		±0.30	±0.05	% of FS
Bipolar Zero Error	B <sub>PZE</sub>	1		±0.15		±0.225	±0.075	% of FS

## 7.0 <u>Life Test/Burn-In Information</u>

- 7.1 HTRB is not applicable for this drawing.
- 7.2 Burn-in is per MIL-STD-883 Method 1015 test condition B or C.
- 7.3 Steady state life test is per MIL-STD-883 Method 1005.

Rev	Description of Change	Date
Α	Initiate	June 26, 2001
В	Update web address. Fix footer	Jan. 25, 2002
С	Update web address.	Aug. 5, 2003
D	Update header/footer & add to 1.0 Scope description.	Feb. 26, 2008
E	Add Absolute Maximum Ratings table in section 3.3	April 2, 2008
F	Updated Section 4.0c note to indicated pre-screen temp testing being performed.	June 6, 2009
G	Updated Fonts and Sizes to ADI standard, enlarged die picture pad numbering	22-Sept-2011