

NOTES:

MATERIALS, MANUFACTURE TO MEET EU RoHS DIRECTIVE, ALL MATERIALS (INCLUDING SOLDERMASK) REFER TO EU RoHS DIRECTIVE 2002/95/EC

LAMINATE & RESIN MATERIALS, Tg>170C, Td>310C

ACCEPTABLE MATERIALS, NELCO N4000-11, NELCO N4000-29, ISOLA IS410, POLYCLAD 370 HR, FR4-08

CLADDING, EXTERNAL LAYERS 1OZ. COPPER, INTERNAL SIGNAL LAYERS 1 OZ. COPPER, INTERNAL PLANE LAYERS 1 OZ. COPPER.

SOLDER MASK, SHALL BE LIQUID PHOTOIMAGABLE (LPI) APPLIED ON BOTH SIDES OVER BARE COPPER AND SHALL MEET IPC-SM-840 (LATEST REV.) CLASS 3.

SILK SCREEN, SHALL BE PERMANENT NON-CONDUCTIVE EPOXY INK, COLOR WHITE.

U.L.F. RATING, 94V0 MINIMUM.

FIDUCIALS; TOP & BOTTOM ARE MIRRORED COPIES, 0,0 @ CENTER U301  
1600, 2075; -1115, 2075; 1530, -2315

## 6 LAYER STACKUP

NOMINAL  
FINISHED  
BOARD  
THICKNESS  
0.625"  
+ / - .007

4.830

 ANALOG  
DEVICES

CERT  
DIVISION  
7910 TRIAD CENTER DR  
GREENSBORO, NC 27409