



DRILL CHART: TOP to BOTTOM

ALL UNITS ARE IN MILS

FIGURE	SIZE	PLATED	QTY
□	8.0	PLATED	118
○	10.0	PLATED	1
⊙	13.0	PLATED	1
⋄	40.0	PLATED	9
⊕	65.0	PLATED	2

TOTAL HOLES: 131

0.000

3.950

4.000 REF

0.050

0.050

0.000

3.950

4.000 REF

0.000

0.002

0.008

0.0015

0.014

0.0015

0.014

0.002

0.042

+/- 10%

TOP COPPER 1.5 oz. 100 ohm differential pair +/-10% line width 0.0055" spacing 0.0045". MICRO STRIP line width 0.0151, TOP LAYER refferenc to Layer 2.

PREPREG ROGERS 4350

PLANE LAYER 2 COPPER 1 oz.

CORE FR4-106

PLANE LAYER 3 COPPER 1 oz.

PREPREG FR4-106

BOTTOM COPPER 1.5 oz

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES

DECIMALS	FRACTIONS	ANGLES
.xx	..010	--1/32
.xxx	..005	-- 2

APPROVAL

DATE

TITLE

DRAWN BY

RLO

10/19/2008

DESIGNED

CHECKED

FINISH

APPROVED

WFG ENGINEER

SIZE

D

FSCM NO

DRAWING NUMBER

FAB_ADCLK846CE01A

REV

A

DO NOT SCALE DWG

SCALE

NONE

SHEET

1 OF 1

ANALOG
DEVICES

TMIC
DIVISION

831 WOBURN STREET
WILMINGTON, MA 01887

FABRICATION DWG.